

**Part Number :** [734154331](#)

**Product Description :** MCX Jack, Right-Angle, PCB Receptacle, Surface Mount, Die Cast Housing with Brass Insert, Nickel (Ni) Plated Outer Contact, Tri-Metal Plated Housing, Tape and Reel, 75 Ohms

**Series Number :** 73366

**Status :** Active

**Product Category :** RF / Coaxial Connectors



## Documents & Resources

### Drawings

[734154331\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Jack, Right-Angle, PCB Receptacle, Surface Mount, Die Cast Housing with Brass Insert, Nickel (Ni) Plated Outer Contact, Tri-Metal Plated Housing, Tape and Reel, 75 Ohms
Application	RF
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	756054934760

### Electrical

Frequency	6 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.559/g
Orientation	Right Angle

Packaging Type	Embossed Tape on Reel
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

---

This document was generated on Sep 17, 2025