Copyright FCI.

FCIconnect.com

PRODUCT NUMBER	PITCH
TSxx11xC00J0G	3.50 mm





Material

- Itemⓐ Clamp: Brass(CuZn),Ni plated
- Itemⓑ Terminal screw: Steel Zinc plating "-" slot type
- Itemⓒ Female contact : PhBz,Tin plated
- Itemⓓ Tob body: Thermoplastic (UL94V-0)
- Itemⓔ Bottom body: Thermoplastic (UL94V-0)
- Itemⓕ With flange screw: Steel M2.5 Zinc plating "+/-" combination type

Electrical cULus VDE

- Voltage rating: 300VAC / 300VAC
- Current rating: 8A / 10A
- Wire range:
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque: 1.7Lb-In / 0.2N.m
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV / 2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval:

PART NO.: TS xx 11 x C 00J0 G

Solid block	0	Black (RAL9005)
No. of poles	2	Red (RAL3001/D)
02 2 poles	3	Orange(RAL2011/P)
03 3 poles	4	Yellow(RAL1018/A)
... ...	5	Green(RAL6018/T)
24 24 poles	6	Blue (RAL5015/A)
	8	Grey(RAL7035/D)
	9	White(RAL1102)
	C	Green(RAL6018/U)

Color

RoHS compliant (lead<4%) In copper Alloy

DIMENSION

Dim A	NX3.5
Dim B	(N-1)X3.5
Dim C	NX3.5+9.6
Dim D	(N-1)X3.5+8.6
Dim E	(N-1)X3.5

N=Number of poles

Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.20
13p-16p	±0.25
17p-24p	±0.30

| | | |