Part Number : 1200910007
Product Description : Nano-Change (M8) Attachable Connectors, Straight Female, 4 Poles
Series Number : 120091
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : N04FA03124



Documents and Resources

Drawings

1200910007_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	120091
Description	Nano-Change (M8) Attachable Connectors, Straight Female, 4 Poles
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Field Attachable Connector
UPC	78678832513

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	3.50-5.00mm (.138-.197")
Coupling Type	Internal Thread
Gender	Female
Keyway	None
Material - Connector Body	Nylon
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	28.716/g
Orientation	Straight
Poles	4
Temperature Range - Operating	0° to +80°C
Wire Size (AWG)	N/A

Downloaded from Arrow.com.

Downloaded from Arrow.com.