Pushing Performance
Since 1945

preLink Terminal mod AWG26/27 white 1=10



Image is for illustration purposes only. Please refer to product description.

Part number	20 82 000 0003
Specification	preLink Terminal mod AWG26/27 white 1=10
HARTING eCatalogue	https://harting.com/20820000003

Identification

Category	Connectors
Series	preLink®
Element	Termination block
Specification	8 poles

Version

Termination method	preLink® IDC insulation displacement termination
Pack contents	10 pieces

Technical characteristics

Conductor cross-section (mm²)	0.1 ... 0.12 mm²
Conductor cross-section (AWG)	AWG 27 ... AWG 26
Wire outer diameter	0.8 ... 1.1 mm
Limiting temperature	-40 ... +85 °C
Mating cycles	≥10
Vibration resistance	5.72 m/s² acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Colour (insert)	White
RoHS	compliant
ELV status	compliant
China RoHS	e

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained


Specifications and approvals

Specifications	EN 45545-2
UL / CSA	UL 1863 DUXR2.E470046 CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	13 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140135482
eCl@ss	27440291 Connector component (parts)
ETIM	EC002943
UNSPSC 24.0	39121400

Wire map



HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.