



# Low Voltage 1:18 Clock Distribution Chip

# MPC9109

**PRODUCT DISCONTINUATION NOTICE - LAST TIME BUY EXPIRES NOVEMBER 21, 2015**

**DATASHEET**

The MPC9109 is a 1:18 low voltage clock distribution chip with 2.5 V or 3.3 V LVCMOS output capabilities. The device features the capability to select either a differential LVPECL or an LVCMOS compatible input. The 18 outputs are 2.5 V or 3.3 V LVCMOS compatible and feature the drive strength to drive 50  $\Omega$  series or parallel terminated transmission lines. With output-to-output skews of 200 ps, the MPC9109 is ideal as a clock distribution chip for the most demanding of synchronous systems. The 2.5 V outputs also make the device ideal for supplying clocks for a high performance Pentium II™ microprocessor based design. For a higher performance version of the 9109 refer to the MPC940L data sheet.

## Features

- LVPECL or LVCMOS clock input
- 2.5 V LVCMOS outputs for Pentium II microprocessor support
- 200 ps maximum output-to-output skew @ 3.3 V output
- Maximum output frequency of 250 MHz @ 3.3 V core
- 32-lead QFP packaging
- Dual or single supply device:
  - Dual  $V_{CC}$  supply voltage, 3.3 V core and 2.5 V output
  - Single 3.3 V  $V_{CC}$  supply voltage for 3.3 V outputs
  - Single 2.5 V  $V_{CC}$  supply voltage for 2.5 V I/O
- For replacement device use 83940DYL

## Functional Description

With a low output impedance ( $\approx 20 \Omega$ ), in both the HIGH and LOW logic states, the output buffers of the MPC9109 are ideal for driving series terminated transmission lines. With a 20  $\Omega$  output impedance the 9109 has the capability of driving two series terminated lines from each output. This gives the device an effective fanout of 1:36. If a lower output impedance is desired please see the MPC942 data sheet. If better performance is desired please see the MPC940L data sheet.

The differential LVPECL inputs of the MPC9109 allow the device to interface directly with a LVPECL fanout buffer like the MC100EP111 to build very wide clock fanout trees or to couple to a high frequency clock source. The LVCMOS input provides a more standard interface for applications requiring only a single clock distribution chip at relatively low frequencies. In addition, the two clock sources can be used to provide for a test clock interface as well as the primary system clock. A logic HIGH on the LVCMOS\_CLK\_Sel pin will select the LVCMOS level clock input. All inputs of the MPC9109 have internal pullup/pulldown resistor so they can be left open if unused.

The MPC9109 is a single or dual supply device. The device power supply offers a high degree of flexibility. The device can operate with a 3.3 V core and 3.3 V output, a 3.3 V core and 2.5 V outputs as well as a 2.5 V core and 2.5 V outputs. The 32-lead QFP package was chosen to optimize performance, board space and cost of the device. The 32-lead TQFP has a 7x7mm body size with a conservative 0.8 mm pin spacing.

## MPC9109

**LOW VOLTAGE  
1:18 CLOCK  
DISTRIBUTION CHIP**



**AC SUFFIX  
32-LEAD LQFP PACKAGE  
Pb-FREE PACKAGE  
CASE 873A-04**

Pentium II is a trademark of Intel Corporation.



Figure 1. Logic Diagram




Figure 2. Pinout: 32-Lead TQFP (Top View)

Table 1. Function Table

LVC MOS CLK_Sel	Input
0	PECL_CLK
1	LVC MOS_CLK

Table 2. Power Supply Voltages

Supply Pin	Voltage Level
VCC1	2.5 V or 3.3 V ± 5%
VCC0	2.5 V or 3.3 V ± 5%

**Table 3. Absolute Maximum Ratings<sup>(1)</sup>**

Symbol	Parameter	Min	Max	Unit
$V_{CC}$	Supply Voltage	-0.3	3.6	V
$V_I$	Input Voltage	-0.3	$V_{CC} + 0.3$	V
$I_{IN}$	Input Current		$\pm 20$	mA
$T_{Stor}$	Storage Temperature Range	-40	125	°C

1. Absolute maximum continuous ratings are those values beyond which damage to the device may occur. Exposure to these conditions or conditions beyond those indicated may adversely affect device reliability. Functional operation under absolute-maximum-rated conditions is not implied.

**Table 4. DC Characteristics** ( $T_A = 0^\circ$  to  $70^\circ\text{C}$ ,  $V_{CCI} = 3.3\text{ V} \pm 5\%$ ;  $V_{CCO} = 3.3\text{ V} \pm 5\%$ )

Symbol	Characteristic	Min	Typ	Max	Unit	Condition
$V_{IH}$	Input HIGH Voltage CMOS_CLK	2.4		$V_{CCI}$	V	
$V_{IL}$	Input LOW Voltage CMOS_CLK			0.8	V	
$V_{PP}$	Peak-to-Peak Input Voltage PECL_CLK	500		1000	mV	
$V_{CMR}$	Common Mode Range PECL_CLK	$V_{CC}-1.4$		$V_{CC}-0.6$	V	
$V_{OH}$	Output HIGH Voltage	2.4			V	$I_{OH} = -20\text{ mA}$
$V_{OL}$	Output LOW Voltage			0.5	V	$I_{OH} = 20\text{ mA}$
$I_{IN}$	Input Current			$\pm 200$	$\mu\text{A}$	
$C_{IN}$	Input Capacitance		4.0		pF	
$C_{pd}$	Power Dissipation Capacitance		10		pF	Per output
$Z_{OUT}$	Output Impedance	18	23	28	$\Omega$	
$I_{CC}$	Maximum Quiescent Supply Current		0.5		mA	

**Table 5. AC Characteristics** ( $T_A = 0^\circ$  to  $70^\circ\text{C}$ ,  $V_{CCI} = 3.3\text{ V} \pm 5\%$ ;  $V_{CCO} = 3.3\text{ V} \pm 5\%$ )

Symbol	Characteristic	Min	Typ	Max	Unit	Condition
$F_{max}$	Maximum Input Frequency			250	MHz	
$t_{PLH}$	Propagation Delay PECL_CLK CMOS_CLK	1.8 1.6	2.8 2.5	3.8 3.3	ns	Note <sup>(1)</sup>
$t_{sk(o)}$	Output-to-Output Skew PECL_CLK CMOS_CLK			200 200	ps	Note <sup>(1)</sup>
$t_{sk(pr)}$	Part-to-Part Skew PECL_CLK CMOS_CLK			2.0 1.7	ns	Note <sup>(1)</sup>
$d_t$	Duty Cycle	45		55	%	Note <sup>(1)</sup>
$t_r, t_f$	Output Rise/Fall Time	0.1		1.3	ns	Note <sup>(1)</sup>

1. Guaranteed by statistical analysis, not 100% tested in production.

**Table 6. Absolute Maximum Ratings<sup>(1)</sup>**

Symbol	Parameter	Min	Max	Unit
V <sub>CC</sub>	Supply Voltage	−0.3	3.6	V
V <sub>I</sub>	Input Voltage	−0.3	V <sub>CC</sub> + 0.3	V
I <sub>IN</sub>	Input Current		±20	mA
T <sub>Stor</sub>	Storage Temperature Range	−40	125	°C

1. Absolute maximum continuous ratings are those values beyond which damage to the device may occur. Exposure to these conditions or conditions beyond those indicated may adversely affect device reliability. Functional operation under absolute-maximum-rated conditions is not implied.

**Table 7. DC Characteristics** (T<sub>A</sub> = 0° to 70°C, V<sub>CCI</sub> = 3.3 V ± 5%; V<sub>CCO</sub> = 2.5 V ± 5%)

Symbol	Characteristic	Min	Typ	Max	Unit	Condition
V <sub>IH</sub>	Input HIGH Voltage CMOS_CLK	2.4		V <sub>CCI</sub>	V	
V <sub>IL</sub>	Input LOW Voltage CMOS_CLK			0.8	V	
V <sub>PP</sub>	Peak-to-Peak Input Voltage PECL_CLK	500		1000	mV	
V <sub>CMR</sub>	Common Mode Range PECL_CLK	V <sub>CC</sub> −1.4		V <sub>CC</sub> −0.6	V	
V <sub>OH</sub>	Output HIGH Voltage	1.8			V	I <sub>OH</sub> = −20 mA
V <sub>OL</sub>	Output LOW Voltage			0.5	V	I <sub>OH</sub> = 20 mA
I <sub>IN</sub>	Input Current			±200	μA	
C <sub>IN</sub>	Input Capacitance		4.0		pF	
C <sub>pd</sub>	Power Dissipation Capacitance		10		pF	Per output
Z <sub>OUT</sub>	Output Impedance		23		Ω	
I <sub>CC</sub>	Maximum Quiescent Supply Current		0.5		mA	

**Table 8. AC Characteristics** (T<sub>A</sub> = 0° to 70°C, V<sub>CCI</sub> = 3.3 V ± 5%; V<sub>CCO</sub> = 2.5 V ± 5%)

Symbol	Characteristic	Min	Typ	Max	Unit	Condition
F <sub>max</sub>	Maximum Input Frequency			250	MHz	
t <sub>PLH</sub>	Propagation Delay PECL_CLK CMOS_CLK	1.8 1.6	2.8 2.5	3.9 3.4	ns	Note <sup>(1)</sup>
t <sub>sk(o)</sub>	Output-to-Output Skew PECL_CLK CMOS_CLK			250 250	ps	Note <sup>(1)</sup>
t <sub>sk(pr)</sub>	Part-to-Part Skew PECL_CLK CMOS_CLK			2.1 1.8	ns	Note <sup>(1)</sup>
d <sub>t</sub>	Duty Cycle	45		55	%	Note <sup>(1)</sup>
t <sub>r</sub> , t <sub>f</sub>	Output Rise/Fall Time	0.1		1.3	ns	Note <sup>(1)</sup>

1. Guaranteed by statistical analysis, not 100% tested in production.

**Table 9. Absolute Maximum Ratings<sup>(1)</sup>**

Symbol	Parameter	Min	Max	Unit
$V_{CC}$	Supply Voltage	-0.3	3.6	V
$V_I$	Input Voltage	-0.3	$V_{CC} + 0.3$	V
$I_{IN}$	Input Current		$\pm 20$	mA
$T_{Stor}$	Storage Temperature Range	-40	125	°C

1. Absolute maximum continuous ratings are those values beyond which damage to the device may occur. Exposure to these conditions or conditions beyond those indicated may adversely affect device reliability. Functional operation under absolute-maximum-rated conditions is not implied.

**Table 10. DC Characteristics** ( $T_A = 0^\circ$  to  $70^\circ\text{C}$ ,  $V_{CCI} = 2.5\text{ V} \pm 5\%$ ;  $V_{CCO} = 2.5\text{ V} \pm 5\%$ )


Symbol	Characteristic	Min	Typ	Max	Unit	Condition
$V_{IH}$	Input HIGH Voltage CMOS_CLK	2.0		$V_{CCI}$	V	
$V_{IL}$	Input LOW Voltage CMOS_CLK			0.8	V	
$V_{PP}$	Peak-to-Peak Input Voltage PECL_CLK	500		1000	mV	
$V_{CMR}$	Common Mode Range PECL_CLK	$V_{CC}-1.0$		$V_{CC}-0.6$	V	
$V_{OH}$	Output HIGH Voltage	1.8			V	$I_{OH} = -12\text{ mA}$
$V_{OL}$	Output LOW Voltage			0.5	V	$I_{OH} = 12\text{ mA}$
$I_{IN}$	Input Current			$\pm 200$	$\mu\text{A}$	
$C_{IN}$	Input Capacitance		4.0		pF	
$C_{pd}$	Power Dissipation Capacitance		10		pF	Per output
$Z_{OUT}$	Output Impedance	18	23	28	$\Omega$	
$I_{CC}$	Maximum Quiescent Supply Current		0.5		mA	

**Table 11. AC Characteristics** ( $T_A = 0^\circ$  to  $70^\circ\text{C}$ ,  $V_{CCI} = 2.5\text{ V} \pm 5\%$ ;  $V_{CCO} = 2.5\text{ V} \pm 5\%$ )

Symbol	Characteristic	Min	Typ	Max	Unit	Condition
$F_{max}$	Maximum Input Frequency			200	MHz	
$t_{PLH}$	Propagation Delay PECL_CLK CMOS_CLK	2.2 2.0	2.8 2.5	4.9 4.2	ns	Note <sup>(1)</sup>
$t_{sk(o)}$	Output-to-Output Skew PECL_CLK CMOS_CLK			250 250	ps	Note <sup>(1)</sup>
$t_{sk(pr)}$	Part-to-Part Skew PECL_CLK CMOS_CLK			2.7 2.2	ns	Note <sup>(1)</sup>
$d_t$	Duty Cycle	45		55	%	Note <sup>(1)</sup>
$t_r, t_f$	Output Rise/Fall Time	0.1		1.3	ns	Note <sup>(1)</sup>

1. Guaranteed by statistical analysis, not 100% tested in production.



PACKAGE DIMENSIONS



© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: LOW PROFILE QUAD FLAT PACK (LQFP) 32 LEAD, 0.8 PITCH (7 X 7 X 1.4)	DOCUMENT NO: 98ASH70029A CASE NUMBER: 873A-04 STANDARD: JEDEC MS-026 BBA	REV: C 01 APR 2005

CASE 873A-04  
ISSUE C  
32-LEAD LQFP PACKAGE

PACKAGE DIMENSIONS



© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE	
TITLE: LOW PROFILE QUAD FLAT PACK (LQFP) 32 LEAD, 0.8 PITCH (7 X 7 X 1.4)	DOCUMENT NO: 98ASH70029A		REV: C
	CASE NUMBER: 873A-04		01 APR 2005
	STANDARD: JEDEC MS-026 BBA		

CASE 873A-04  
ISSUE C  
32-LEAD LQFP PACKAGE

## PACKAGE DIMENSIONS

### NOTES:

1. DIMENSIONS ARE IN MILLIMETERS.
2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5–1994.
3. DATUMS A, B, AND D TO BE DETERMINED AT DATUM PLANE H.
4. DIMENSIONS TO BE DETERMINED AT SEATING PLANE DATUM C.
5. DIMENSION DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL NOT CAUSE THE LEAD WIDTH TO EXCEED THE MAXIMUM DIMENSION BY MORE THAN 0.08 MM. DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OR THE FOOT. MINIMUM SPACE BETWEEN PROTRUSION AND ADJACENT LEAD OR PROTRUSION: 0.07 MM.
6. DIMENSIONS DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE PROTRUSION IS 0.25 MM PER SIDE. DIMENSIONS ARE MAXIMUM PLASTIC BODY SIZE DIMENSIONS INCLUDING MOLD MISMATCH.
7. EXACT SHAPE OF EACH CORNER IS OPTIONAL.
8. THESE DIMENSIONS APPLY TO THE FLAT SECTION OF THE LEAD BETWEEN 0.1 MM AND 0.25 MM FROM THE LEAD TIP.

© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.		MECHANICAL OUTLINE		PRINT VERSION NOT TO SCALE	
TITLE:  LOW PROFILE QUAD FLAT PACK (LQFP) 32 LEAD, 0.8 PITCH (7 X 7 X 1.4)			DOCUMENT NO: 98ASH70029A		REV: C
			CASE NUMBER: 873A-04		01 APR 2005
			STANDARD: JEDEC MS-026 BBA		

PAGE 3 OF 3

**CASE 873A-04  
ISSUE C  
32-LEAD LQFP PACKAGE**



Revision History Sheet

Rev	Table	Page	Description of Change	Date
3		1	NRND – Not Recommend for New Designs	12/19/12
4		1	PDN# CQ-14-08	12/8/14

## We've Got Your Timing Solution



6024 Silver Creek Valley Road  
San Jose, California 95138

**Sales**  
800-345-7015 (inside USA)  
+408-284-8200 (outside USA)  
Fax: 408-284-2775  
[www.IDT.com/go/contactIDT](http://www.IDT.com/go/contactIDT)

**Technical Support**  
[clocks@idt.com](mailto:clocks@idt.com)  
+480-763-2056

DISCLAIMER Integrated Device Technology, Inc. (IDT) and its subsidiaries reserve the right to modify the products and/or specifications described herein at any time and at IDT's sole discretion. All information in this document, including descriptions of product features and performance, is subject to change without notice. Performance specifications and the operating parameters of the described products are determined in the independent state and are not guaranteed to perform the same way when installed in customer products. The information contained herein is provided without representation or warranty of any kind, whether express or implied, including, but not limited to, the suitability of IDT's products for any particular purpose, an implied warranty of merchantability, or non-infringement of the intellectual property rights of others. This document is presented only as a guide and does not convey any license under intellectual property rights of IDT or any third parties.

IDT's products are not intended for use in applications involving extreme environmental conditions or in life support systems or similar devices where the failure or malfunction of an IDT product can be reasonably expected to significantly affect the health or safety of users. Anyone using an IDT product in such a manner does so at their own risk, absent an express, written agreement by IDT.

Integrated Device Technology, IDT and the IDT logo are registered trademarks of IDT. Other trademarks and service marks used herein, including protected names, logos and designs, are the property of IDT or their respective third party owners.

Copyright 2012. All rights reserved.