Part Number : 1200698639
Product Description : Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, A-Coded, Male (90°) to Pigtail, 22 AWG, Shielded WSOR Cable, 10.0m (32.81') Length
Series Number : 120069
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 805S07BS1M100



Documents and Resources

Drawings

1200698639_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120069
Description	Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, A-Coded, Male (90°) to Pigtail, 22 AWG, Shielded WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	889056131605

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	6.10mm (.240")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Knurled Hexnut, Threaded
Gender	Male-Pigtail
Keyway	A-Coded

Downloaded from Arrow.com.

LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	WSOR
Wire Size (AWG)	22

Downloaded from Arrow.com.