



© 2021 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER PCN-21-108720	05AUG2021	DRK	IG
	B2	REVISED PER PCN-26-280905	15JUN2026	JT	EC









8 SURFACE FINISH: 32 RMS OR BETTER; ⏥ | .005 [.12].

7 RECOMMENDED SCREW: 4-20 [M3.12 x 1.27] THREAD-FORMING SCREW.
TORQUE: 6-10 IN-LB [.68-1.13 NM].

6 RECOMMENDED SCREW: 6-19 [M3.63 x 1.34] THREAD-FORMING SCREW.
TORQUE: 10-20 IN-LB [1.13-2.25 NM].

5 SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.

4. THIS RECEPTACLE MATES WITH DTM06-12S*-**** PLUG
(*=A,B,C,D KEYS; ****=ALL MODIFICATIONS).

3. CONTACT PLATING - MATING SIDE: NICKEL; PCB SIDE: TIN

2 MATERIAL -
HOUSING & PA46 GF30; GRAY
SLEEVE RETAINER PA46 GF10 (SEE SHEET 2 FOR COLORS)
SEALS: VMQ (RED-ORANGE)
PINS: COPPER ALLOY

1. PANEL CUTOUT:±.010 [.25].

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±.025 [.64mm]
0 PLC ±-
1 PLC ±
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±

MATERIAL 2

FINISH -

DWN	D MEYER 24APR2002
CHK	R MESSENGER 21FEB2007
APVD	D MEYER 21FEB2007
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-

TE Connectivity

NAME RECEPTACLE 12 #20 SIZE CONTACTS
KEY ARRANGEMENTS A, B, C AND D
180 DEG, DTM SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	11139	C-DTM15-12PX	-

CUSTOMER DRAWING | SCALE 3:2 | SHEET 1 OF 2 | REV B2


1470-19 (3/13)

Downloaded from Arrow.com.

© 2021 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

DTM15-12PA
KEY: -A-




3X KEYWAY
SLEEVE RETAINER: GRAY

DTM15-12PB
KEY: -B-




3X KEYWAY
SLEEVE RETAINER: BLACK

DTM15-12PC
KEY: -C-





3X KEYWAY
SLEEVE RETAINER: GREEN

DTM15-12PD
KEY: -D-



3X KEYWAY
SLEEVE RETAINER: BROWN





RECOMMENDED PANEL CUTOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±.025 [.64mm]

0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL 2

FINISH - -

DWN	D MEYER	24APR2002
CHK	R MESSENGER	21FEB2007
APVD	D MEYER	21FEB2007
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	

TE Connectivity

NAME: RECEPTACLE 12 #20 SIZE CONTACTS KEY ARRANGEMENTS A, B, C AND D 180 DEG, DTM SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	11139	C-DTM15-12PX	-

CUSTOMER DRAWING | SCALE 3:2 | SHEET 2 OF 2 | REV B2

Downloaded from Arrow.com.