



Power Versa-Lock | Power Versa-Lock 5.0

TE Internal #: 2325349-3

Gang Wire Seal, -30 – 140 °C [-22 – 284 °F], Blue, Silicone Rubber,
2.45 – 3.6 mm [.097 – .142 in] Insulation Diameter, Power Versa-Lock
5.0

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Gang Wire Seal**
Operating Temperature Range: **-30 – 140 °C [-22 – 284 °F]**
Primary Product Color: **Blue**
Primary Product Material: **Silicone Rubber**
Compatible Insulation Diameter Range: **2.45 – 3.6 mm [.097 – .142 in]**

Features

Product Type Features

Connector Seal & Plug Type	Gang Wire Seal
----------------------------	----------------

Configuration Features

Number of Positions	3
---------------------	---

Body Features

Primary Product Color	Blue
Primary Product Material	Silicone Rubber

Dimensions

Compatible Insulation Diameter Range	2.45 – 3.6 mm[.097 – .142 in]
--------------------------------------	-------------------------------

Usage Conditions

Operating Temperature Range	-30 – 140 °C[-22 – 284 °F]
Operating Temperature (Max)	140 °C[284 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted



	Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in M-43213-1) Decamethylcyclopentasiloxane (D5) (.5% in M-43213-1) Octamethylcyclotetrasiloxane (D4) (.5% in M-43213-1) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-2336231-6
Power Versa-Lock TL CAP, 2X3 KEY C



TE Part # 2-2378159-3
Power Versa-Lock PLUG, 1X3 KEY B



TE Part # 776363-1
SEALING PLUG, SZ 16 CAVITY



TE Part # 1-2381315-3
Power Versa-Lock PLUG, 1X3 KEY A, GWT



TE Part # 2-2378158-3
Power Versa-Lock CAP, 1X3 KEY B

TE Part # 1-2378158-3
Power Versa-Lock CAP, 1X3 KEY A

TE Part # 1-2336231-6
Power Versa-Lock TNL CAP, 2X3 KEY A

TE Part # 3-2378158-3
Power Versa-Lock CAP, 1X3 KEY C

TE Part # 1-2336229-6
Power Versa-Lock PLUG, 2X3 KEY A

TE Part # 3-2337219-6
PWR VERSA-LOCK CAP, 2X3 KEY C

TE Part # 1-2378159-3
Power Versa-Lock PLUG, 1X3 KEY A

TE Part # 1-2381608-6
Power Versa-Lock TNL CAP, 2X3 KEY A, GWT

TE Part # 3-2378159-3
Power Versa-Lock PLUG, 1X3 KEY C

TE Part # 2-2337219-6
PWR VERSA-LOCK CAP, 2X3 KEY B

TE Part # 1-2337219-6
Power Versa-Lock CAP, 2X3 KEY A

TE Part # 2-2336231-6
Power Versa-Lock TNL CAP, 2X3 KEY B

TE Part # 3-2336229-6
Power Versa-Lock PLUG, 2X3 KEY C

TE Part # 2-2336229-6
Power Versa-Lock PLUG, 2X3 KEY B

Also in the Series | Power Versa-Lock 5.0

Connector Contacts(12)

Connector Hardware(5)

Connector Seals & Cavity Plugs(10)


Power Contacts(12)



Rectangular Connector Housings(77)



Rectangular Power Connectors(77)



Standard Rectangular Connectors(77)

Customers Also Bought



TE Part #816484-SF
RN102-0.3-02-12M




TE Part #8-1879494-9
CRGH0603 5% 4K7 0.2W




TE Part #9-1879517-0
CRGH1206 1% 22R 0.5W




TE Part #3-2176330-7
CRGP 2010 10K 1%



TE Part #2-2176348-5
CRGCQ 2010 10K 5%



TE Part #4-2176397-1
3502 47R 1%



TE Part #2-2176406-5
3560 10R 1%



TE Part #2176492-9
BMC 0402 120R 25% A Gen C



TE Part #2376595-2
250 FASTON PCB TAB TPBR



TE Part #1-2378158-3
Power Versa-Lock CAP, 1X3 KEY A

Documents

Product Drawings

Power Versa-Lock REAR SEAL, 1X3, LargeID

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2325349-3_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2325349-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2325349-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[power-versa-lock-connectors-0421](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English