



Part Number : 1052620002

Series Number : 105262

Product Category : Antennas

Product Description : ISM 868/915MHz  
Antenna, 150.00mm Cable Length,  
Compatible with U.FL / I-PEX MHF Connectors

Status : Active

Documents & Resources


Drawings  
[Drawing 1052620002\\_sd.pdf](#)

3D Models and Design Files  
[3D Model 1052620002\\_stp.zip](#)

Specifications  
[Application Specification AS-105262-0001-001.pdf](#)  
[Packaging Specification PK-105262-001-001.pdf](#)  
[Product Specification PS-105262-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Antennas
Series	105262
Description	ISM 868/915MHz Antenna, 150.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Family	Industrial, Scientific and Medical (ISM) Antennas
Product Name	ISM 868/915 MHz Stand Alone
Protocol	LoRa, Neul, SigFox, Z-Wave, Zigbee
Type	Internal, ISM Antenna, LPWAN
UPC	887191106540

#### Electrical

Band#1 F_End (MHz)	870
Band#1 F_Start (MHz)	863
Band#2 F_End (MHz)	928
Band#2 F_Start (MHz)	902
Electrical Connectivity	Cable
Peak Gain (dBi)	0.3 @ 868 MHz, 1.3 @ 915 MHz
Return Loss - S11 (dB)	< -6
Total Efficiency	> -1.9dB @ 915 MHz, > -3.1dB @ 868 MHz

#### Physical

Cable Length	150.00mm
Length	79.00mm
Mounting Style	Adhesive

Net Weight	0.755/g
Packaging Type	Tray
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	10.00mm

---

Mates With / Use With

Mates with Part(s)

Description	Part Number
50 Ohms, MCRF, PCB Vertical Jack Receptacle, SMT, 1.25mm Mounted Height	<u>734120110</u>

---

This document was generated on May 06, 2024