

Part Number : 1300108029
Product Description : Mini-Change Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 AWG, Gray PUR Cable, 1.0m (3.28') Length, Zinc Die-Cast Coupling Nut
Series Number : 130010
Status : Obsolete
Product Category : Industrial Cable Assemblies
Engineering Part Number : 115030B21M010

Documents and Resources

Drawings

1300108029_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Obsolete

Downloaded from Arrow.com.

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Industrial Cable Assemblies
Series	130010
Description	Mini-Change Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 AWG, Gray PUR Cable, 1.0m (3.28') Length, Zinc Die-Cast Coupling Nut
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Double Ended
UPC	887191260730

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

Physical

Cable Diameter	12.70mm (.500")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PUR

Obsolete

Downloaded from Arrow.com.

Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	179.500/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	UL 20233
Wire Size (AWG)	16

Obsolete

Downloaded from Arrow.com.