

1. MATERIALS

- HOUSING: THERMOPLASTIC, FLAMMABILITY RATING UL 94V-0.
- SHIELD: BRASS 0.20mm THICK, PREPLATED WITH 0.76um MIN SEMI-BRIGHT NICKEL. SOLDER TABS POST DIPPED WITH 2.54um MIN SAC SOLDER.
- CONTACTS: PHOSPHOR BRONZE 0.46mm X 0.30mm, PHOSPHOR BRONZE, 1.27um MIN NICKEL UNDERPLATE, WITH 1.27um MIN GOLD PLATING AT MATING INTERFACE AND 2.54um MIN MATTE TIN ON SOLDER TAILS, OR 1.27um MIN NICKEL UNDERPLATE, WITH 0.05um GOLD PLATING OVER 0.76um MIN PALLADIUM NICKEL PLATING AT MATING INTERFACE AND 2.54um MIN MATTE TIN ON SOLDER TAILS.
- SOLDER TAILS: 0.25mm THICK, PHOSPHOR BRONZE, 1.27um MIN OVERALL NICKEL UNDERPLATE, 3um TIN PLATE
- LIGHT EMITTING DIODE (LED): DIFFUSED EPOXY LENS, 0.5mm X 0.5mm CARBON STEEL WIREFRAME LEADS PREPLATED WITH 2.03um MIN. SILVER PLATE OVER 1.02um MIN. NICKEL OVER 1.02um MIN. COPPER UNDERPLATE; LEADS POST-PLATED WITH 3.05um MIN. MATTE TIN AND/OR SAC SOLDER DIP OR PURE TIN SOLDER DIP

2 RJ45 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68 SUB PART F.

③ MAGNETICS

- APPLICATION: 10/100/1000 BASE-T, EXTENDED TEMPERATURE
- IMPEDANCE: 100 OHMS
- TURNS RATIO (CHIP: CABLE): 1:1 ALL FOUR PAIRS
- OPEN CIRCUIT INDUCTANCE (OCL): 350uH MIN. @100kHz, 0.1VRMS, 8mADC BIAS FROM -40°C TO +85°C, ALL FOUR PAIRS
- ALL FOUR PAIRS BI-DIRECTIONAL
- PERFORMANCE @ 25°C:
 - INSERTION LOSS (IL): 1.1dB MAX. FROM 0.5MHz TO 100MHz
 - RETURN LOSS (RL): 18dB MIN FROM 0.5MHz TO 40MHz
 - 12-20LOG(f/80)dB MIN. FROM 40.1MHz TO 100MHz
 - CROSSTALK ATTENUATION: 35dB MIN. FROM 0.5MHz TO 40MHz
 - 33-20LOG(f/50)dB MIN. FROM 40.1MHz TO 100MHz
 - COMMON MODE REJECTION RATIO (CMRR): 30dB MIN. FROM 0.5MHz TO 100MHz
- ISOLATION VOLTAGE: 2250VDC FOR 60 SECONDS WITH A RISE TIME OF 500 V/SEC

4. OPERATING TEMPERATURE: FROM -40°C TO +85°C.












5 INDICATED MAGNETIC CONNECTIONS ARE SYMMETRICAL TO SUPPORT AUTO-MDI/MDIX.



△6. LEDS ARE DRIVEN WITH CONSTANT CURRENT AT APPROX 20mA
LED COLOR: DOMINATE WAVELENGTH (λD): GREEN 568 nm TYP. AT IF = 20mA
FORWARD VOLTAGE (VF): GREEN 2.2V TYP. at IF = 20mA
DOMINATE WAVELENGTH (λD): YELLOW 588 nm TYP. AT IF = 20mA
FORWARD VOLTAGE (VF): YELLOW 2.1V TYP. at IF = 20mA
DOMINATE WAVELENGTH (λD): ORANGE 605 nm TYP. AT IF = 20mA
FORWARD VOLTAGE (VF): ORANGE 2.1V TYP. at IF = 20mA


7. TRP CONNECTOR LOGO, PART NUMBER, DATE CODE, COUNTRY OF ORIGIN AND AGENCY APPROVAL MARKING IN APPROXIMATE LOCATION SHOWN. DATE CODE: YYWW D WHERE YY IS YEAR. WW IS WORK WEEK. D IS DAY OF WEEK, WITH SUNDAY=1.

8 PART SHOULD BE RECOMMENDED FOR WAVE SOLDERING PROCESS, PREHEAT TEMPERATURE IS 120°C TO 160°C, 120 SECONDS TO 180 SECONDS, PEAK WAVE SOLDERING TEMPERATURE IS 260°C MAX, 10 SECONDS MAX.


9 PART SHOULD BE RECOMMENDED FOR IR REFLOW SOLDERING PROCESS, PEAK SOLDERING TEMPERATURE IS 260°C MAX, DURATION TIME IS 10 SECONDS MAX, OVER 230°C WITHIN 40-60 SECONDS.

	TAPE AND REEL	1.65	N/A		N/A		2250015-7
	TAPE AND REEL	1.65	GREEN	-	GREEN	-	2250015-6
	TRAY	1.65	GREEN	YELLOW	GREEN	-	2250015-5
	TRAY	1.27	GREEN	YELLOW	GREEN	YELLOW	2250015-4
	TRAY	1.27	GREEN	ORANGE	YELLOW	-	2250015-3
	TRAY	1.27	GREEN	YELLOW	GREEN	-	2250015-2
	TRAY	1.27	GREEN	-	GREEN	-	2250015-1
SOLDERING PROCESS	PACKAGE METHOD	DIM A	11  12	12  11	13  14	14  13	PART NUMBER
			LED 1		LED 2		


THIS DRAWING IS A CONTROLLED DOCUMENT. AND COMPLIANT TO ASME Y14.5M		DWN: ROY LIU 13MAY2013 CHN: CHY LIU 13MAY2013 APP: TOWER YU/ FRANK LIU TONY YUAN 13MAY2013		 trp CONNECTOR a bel group		DONGGUAN CHINA	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLG ±0.25 1 PLG ±0.25 2 PLG ±0.25 3 PLG ±0.25 4 PLG ±0.25 ANGLES ±°		MODEL NAME MAGJACK SINGLE NON-PoE		DESC 1X1 7G140ET GIGABIT TAB UP W/ LED	
		APPLICATION SPEC		SIZE A1		CAGE CODE C=2250015	
PRODUCT SPEC				DRAWING NO		RESTRICTED TO	
				SCALE 4:1		SHEET 1 of 2 REV A	
CUSTOMER DRAWING							



SUGGESTED CUSTOMER BOARD LAYOUT
(COMPONENT SIDE)




2250015-5
2250015-6 SHOWN




2250015-7 SHOWN
(WITHOUT LED)

7G140ET GIGABIT CIRCUIT



C1=1000pF, 2KV, CAPACITOR
C2 - C5 : 0.1uF, CAPACITORS
R1 - R4 : 75 Ohms, RESISTORS

THIS DRAWING IS A CONTROLLED DOCUMENT. AND COMPLIANT TO ASME Y14.5M		OWN ROY LIU 13MAY2013	 trp CONNECTOR a bel group		DONGGUAN CHINA	
DIMENSIONS: mm		CHK TOWER YU/ FRANK LIU 13MAY2013				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV TONY YUAN 13MAY2013	MODEL NAME MAGJACK		DESC 1X1 7G140ET GIGABIT TAB UP W/ LED	