APC NetShelter Metered Rack PDU, 0U, 17.3kW, 208V, 3 phase, 60A, 30 C13 outlets

AP8867

Overview

Lead time Usually in Stock

Main

Colour	Black	
Product or component type	PDU	
PDU type	Metered	
Cord length	1.82 m	
Number of cables	1	
Provided equipment	Installation guide Rack mounting brackets Serial configuration cable Safety guide	

Complementary

Input Voltage	208 V 3 phases	
Height	1829 mm	
Width	56 mm	
Output Voltage	208 V	
Depth	51 mm	
Net weight	10.2 kg	
Mounting location	Side	
Mounting preference	No preference	
Input Plug Type	IEC 60309 60 A 3P + PE	
Mounting mode	Rack-mounted	
Rack units	0U	
Mounting position	Vertical	
[In] rated current	48 A	
Max line current	48 A	
Input current limits	60 A	
Load capacity	17300 VA	
Network frequency	50/60 Hz	
Outlet type and quantity	30 IEC 60320 C13	

Environment

Product certifications	cUL listed	
	UL listed	
	VCCI class A	
Standards	EN 55022 class A	
	EN 55024	
	EN 61000-3-2	
	EN 61000-3-3	
	FCC part 15 class A	
Ambient air temperature for operation	-560 °C	
Relative humidity	595 %	
Operating altitude	010000 ft	
Ambient air temperature for storage	-2565 °C	
Storage Relative Humidity	595 %	
Storage altitude	015240 m	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	214.9 cm
Package 1 Width	11.2 cm
Package 1 Length	22.1 cm
Package 1 Weight	14.05 kg

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	6421
Environmental Disclosure	Product Environmental Profile

Use Better

─────────────────────────────────────	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration
Halogen-free status	Product contains halogen above thresholds
☼ Energy efficiency	
Energy Efficiency Optimized	Energy efficient product

Use Again

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Removable battery	Yes
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product data sheet

AP8867

Image of product / Alternate images

Alternative



Downloaded from Arrow.com.

