

[Harnessing](#) > [Heat Shrink Components](#) > [Breakouts/Transitions](#)

322A434-25/225-0



Raychem

TE Internal #: **280291-000**

Alias #: **4-1192074-8**

Molded Part Shape : **T Shape**

Number of Branches/Legs : **3**

Material Code : **25**

Material Systems Code : **25**

Adhesive Pre-Coat : **Yes**

[Similar Products](#)

[Compatible Parts & Tooling](#)

We are here to help!

Get in touch with our product experts.



[CHAT WITH US](#)



[EMAIL US](#)



[CALL US](#)

Feedback

Documents	Features	Product Compliance
Product Drawings	322A434-25/225-0 322A434-25/225-0 English	
Datasheets & Catalog Pages	1654025_Sec4_-25 ENG_CS_1654025_Sec4_-25_0313.pdf English	
Product Specifications	-25 MOULDED PARTS ENG_SS_RW-2070_2.pdf English ENG_SS_RW-2074_2.pdf English	
Product Environmental Compliance	Safety Datasheet ENG_MSDS_RAY3111-EC-ENG_2018-08-31.pdf English FRE_MSDS_RAY3111-EC-FRE_2018-08-28.pdf French Safety Datasheet GER_MSDS_RAY3111-EC-GER_2018-08-28.pdf German Safety Datasheet ITA_MSDS_RAY3111-EC-ITA_2018-08-28.pdf Italian Safety Datasheet SPA_MSDS_RAY3111-EC-SPA_2018-08-28.pdf Spanish Safety Datasheet SWE_MSDS_RAY3111-EC-SWE_2018-08-28.pdf Swedish Safety Datasheet	

 [DUT_MSDS_RAY3111-EC-DUT_2018-08-28.pdf](#)

Dutch

Safety Datasheet

 [DAN_MSDS_RAY3111-EC-DAN_2018-08-28.pdf](#)

Danish

Safety Datasheet

 [FRE_MSDS_SDS0190-EC-FRE_2014-04-10.pdf](#)

French

Safety Datasheet

 [ITA_MSDS_SDS0190-EC-ITA_2014-04-10.pdf](#)

Italian

Safety Datasheet

 [DUT_MSDS_SDS0190-EC-DUT_2014-04-10.pdf](#)

Dutch

Safety Datasheet

 [DAN_MSDS_SDS0190-EC-DAN_2014-04-10.pdf](#)

Danish

Safety Datasheet

 [ENG_MSDS_SDS0190-EC-ENG_2014-04-10.pdf](#)

English

Safety Datasheet

 [GER_MSDS_SDS0190-EC-GER_2014-04-10.pdf](#)

German

Safety Datasheet

 [NOR_MSDS_SDS0190-EC-NOR_2014-04-10.pdf](#)

Norwegian

Safety Datasheet

 [SPA_MSDS_SDS0190-EC-SPA_2014-04-10.pdf](#)

Spanish

Safety Datasheet

 [SWE_MSDS_SDS0190-EC-SWE_2014-02-21_SDS190ECW.pdf](#)

Swedish

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type
Features

Molded Part Shape : **T Shape**
Size Code : **434**

Configuration
Features

Number of Branches/Legs : **3**

Body Features

Material Code : **25**
Material Systems Code : **25**
Adhesive Pre-Coat : **Yes**
Material : **Fluid Resistant Modified Elastomer**

Dimensions

Inside Diameter Range (Leg 1) : **15.3 – 30.4 mm [.6 – 1.2 in]**
Inside Diameter Range (Body) : **15.2 – 30.5 mm [.6 – 1.2 in]**
Inside Diameter Range (Leg 2) : **10.2 – 20.3 mm [.4 – .8 in]**

Usage Conditions

Operating Temperature Range : **-75 – 150 °C [-103 – 302 °F]**



Operation/Application	Power Cable Accessory : No
Industry Standards	Government Qualified : No
Other	Molded Part Shape Code : 322A Fluid/Chemical Resistance : Long-Term Exposure at High Temperature Adhesive Options : /225 Precoat Adhesive Type : High Performance Pre-Coat Adhesive Adhesive Code : 225
EU RoHS Directive 2011/65/EU	
EU RoHS Directive with Phthalates Amendment 2011/65/EU, 2015/863/EU	<i>The 4 Phthalates substances of amendment 2015/863/EU only become restricted as of 22 July 2019 for all electrical and electronic equipment, apart from Categories 8 (medical devices) and 9 (monitoring and control equipment) for which the restriction applies as of 22 July 2021.</i>
EU ELV Directive 2000/53/EC	
China RoHS 2 Directive MIIT Order No 32, 2016	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	
Solder Process Capability	Not applicable for solder process capability
Statement of Compliance	Statement of Compliance pdf
Compliance Documents	There may be Environmental Compliance related documents on the DOCUMENTATION Tab
Disclaimer	This information is provided based on reasonable inquiry of our suppliers and represents our current

actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

TOP RESULTS ?

BREAKOUTS/TRANSITIONS
322A434-25/225-0



Non-Stocked

Molded Part Shape : T Shape
Number of Branches/Legs : 3
Material Code : 25
Material Systems Code : 25
Adhesive Pre-Coat : Yes


BREAKOUTS/TRANSITIONS
322A434-25-0



From **In-Stock**

Molded Part Shape : T Shape
Number of Branches/Legs : 3
Material Code : 25
Material Systems Code : 25
Adhesive Pre-Coat : No


BREAKOUTS/TRANSITIONS
322A514-25-03/225-0



Non-Stocked

Molded Part Shape : T Shape
Number of Branches/Legs : 3
Material Code : 25
Material Systems Code : 25
Adhesive Pre-Coat : Yes

BREAKOUTS/TRANSITIONS
322A412-25/225-0



Non-Stocked

Molded Part Shape : T Shape
Number of Branches/Legs : 3
Material Code : 25
Material Systems Code : 25
Adhesive Pre-Coat : Yes

