




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		B	EC 0G3C 0224 05	11MAY05	BSV JLG
			B1	REVISED PER ECO-09-023929	24OCT09	KK AEG

- 1 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 POSTS: .000030 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 4 POSTS: .000030 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5 OBSOLETE	4	.806	.106	1.032	.900	9	20	5-1571311-1
	3	.806	.106	1.032	.900	9	20	1571311-1
	PLATING	E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	06JUN02	Tyco Electronics Corporation Harrisburg, Pa 17105-3608
DIMENSIONS: INCHES		CHK J GESFORD	06JUN02	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J GESFORD	06JUN02	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC		
MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK; POSTS - Cu-Ni-Sn		APPLICATION SPEC		HDR ASSY, MOD II, COMPLIANT PIN, DBL ROW, .100X.100 CL, 4 SIDED SHROUD, FOR .062 THICK PCB
FINISH: SEE TABLE		WEIGHT -		
		CUSTOMER DRAWING		
A2 00719 C=1571311				RESTRICTED TO
SCALE 4:1				SHEET 1 OF 1
				REV B1