


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASED DRAWING	Jul-16-18	Flan	Tommy



CONTACT ORIENTATION ON ROLL(3000PCS/COIL)

NOTES : (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL :

- 1.1. CONTACT BODY : COPPER ALLOY.
1.2. OUTER SPRING : STAINLESS STEEL.

2. SPECIFICATIONS :

- 2.1 CURRENT RATING : 13A MAX.
2.2 TERMINATION TYPE : CRIMPING.
2.3 WIRE RANGE : 26~24AWG.
2.4 WIRE INSULATION DIA(MAX) : ϕ 2.1mm.





3. RoHS COMPLIANT.

4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

5. AVAILABLE TOOLS :

- 5.1 HAND CRIMPER : MFX-3954.
5.2 CRIMP APPLICATOR : MFX-3957.
5.3 EXTRACTION TOOL : QXRT16.

P/N	CONTACT PLATING(MATING AREA)
SP24M2T	TIN PLATING OVER NICKEL.
SP24M2N	NICKEL PLATING OVER COPPERIZE.
SP24M2F	GOLD FLASH PLATING OVER NICKEL.
SP24M2G5	5 μ "GOLD PLATING OVER NICKEL.
SP24M2G10	10 μ "GOLD PLATING OVER NICKEL.
SP24M2G15	15 μ "GOLD PLATING OVER NICKEL.
SP24M2G30	30 μ "GOLD PLATING OVER NICKEL.



QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED			
1) All dimensions are in millimeters.			
2) Tolerances are as follows:			
1 PL DEC 40.30 Fractions 1/104			
3 PL DEC 40.08 Angles 1°			
3) Note reference = 			
MATERIAL SPECIFICATIONS:			
SIGNATURES		DATE	
DRAWN: Hm		Jul-16-18	
CHECKED: Jd		Jul-16-18	
ENGINEER:		APPROVAL: Tommy	
CUSTOMER:		Jul-16-18	
THIS DRAWING IS SUBMITTED FOR INFORMATION ONLY. IT IS NOT TO BE USED FOR PRODUCTION. SPECIFICATIONS AND PERFORMANCE DATA OF REPRODUCTION ARE LIMITED. ALL MANUFACTURING VARIATIONS.			
PROCESS SPECIFICATIONS:			
NEXT ASSTY:			

Sine Systems - www.amphenor-sine.com			
44724 Moley drive			
Clinton Township, MI 48036			
ECO-MATE PIN CONTACT,			
STAMPED 26-24AWG SIZE 16			

SIZE	TYPE	DWG NO.	REVISION
B	C-	SP24M2XX	A1
SCALE	NONE	SHEET 1	OF 1