

6

5

4

3

2


1

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/6/13	


APPROVED: _____

DATE: _____ TITLE: _____


D



C




RECOMMENDED PCB LAYOUT



D

B



B

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Brass, Nickel plated

Plating:

30u" Gold over Nickel underplate on contact area,

Tin over Copper underplate on SMT tails

Electrical:

Operating voltage: 30 VAC max.

Current rating: 1 Amp max.

Contact resistance: 30 mohms max.

Insulation resistance: 1,000 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.

PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM
TOLERANCES: EXCEPT AS NOTED

XX ± 0.25
.XXX ± 0.20

APPROVALS		DATE
DRAWN	AY	6/6/13
CHECKED	AH	6/6/13
APPROVED		

TITLE

ADAM TECH
909 Rarway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MINI USB, TYPE B, 5PIN, VERTICAL, SMT

SIZE	PART NO.	REV.
X	MUSB-B5-S-VT-SMT-PP-T/R	-
REF:	S00126T	SCALE: NTS SHEET 1 OF 1

A

A

6

5

4

3

2

1