




**Part Number :** [1511181034](#)

**Product Description :** Milli-Grid PCB Header, 2.00mm Pitch, Vertical, Surface Mount, Dual Row, 2.00µm Tin (Sn) Plating, without Peg, without Pick and Place Cap, 34 Circuits, Glow-Wire Capable, Tube

**Series Number :** 151118

**Status :** Active

**Product Category :** PCB Headers and Receptacles



---

## Documents and Resources

### Drawings

[1511181034 sd.pdf](#)

[PK-151118-0001-001.pdf](#)

[PK-151118-3000-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[503940001-AS-000.pdf](#)


[503940002-AS-000.pdf](#)

[PS-151117-0001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	151118
Description	Milli-Grid PCB Header, 2.00mm Pitch, Vertical, Surface Mount, Dual Row, 2.00µm Tin (Sn) Plating, without Peg, without Pick and Place Cap, 34 Circuits, Glow-Wire Capable, Tube
Application	Board-to-Board, Wire-to-Board, Signal
Component Type	PCB Header
Product Name	Milli-Grid
UPC	889056794008

### Agency

CSA	LR19980
UL	E29179

## Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V AC

## Physical

Breakaway	No
Circuits (Loaded)	34
Circuits (maximum)	34
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	1.471/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tube
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	2.000µm
Plating min - Termination	2.000µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Surface Mount

## Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Milli-Grid Dual Row Receptacle Housings	<u>151192</u>
Milli-Grid Dual Row Receptacle Housings	<u>51110</u>
Milli-Grid Vertical Through Hole PCB Receptacles	<u>78787</u>
Milli-Grid Top Entry Surface Mount PCB Receptacles	<u>78788</u>
Milli-Grid Vertical Through Hole PCB Receptacles	<u>79107</u>
Milli-Grid Top/Bottom Entry Surface Mount PCB Receptacles	<u>79109</u>

---

This document was generated on May 14, 2026