



**Part Number :** [887689810](#)

**Product Description :** HDMI-to-HDMI Cable Assembly, 28 AWG, 2.0m Length

**Series Number :** 88768

**Status :** Obsolete

**Product Category :** I/O Cable Assemblies


## Documents and Resources

### Specifications

[PS-88768-002-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains C,C'-azodi(formamide) per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

Status	Obsolete
Category	I/O Cable Assemblies
Series	88768
Description	HDMI-to-HDMI Cable Assembly, 28 AWG, 2.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	HDMI-to-HDMI
Product Name	HDMI
UPC	756054858448

### Electrical

Current - Maximum per Contact	0.5A
Impedance	100Ω
Shielded	Yes
Voltage - Maximum	40V

### Physical

Cable Length	2.0m
Circuits (Loaded)	19
Circuits (maximum)	19
Color - Resin	Natural
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Low Density Polyethylene
Net Weight	143.150/g

Packaging Type	Bag
Plating min - Mating	0.813µm
Plating min - Termination	1.270µm
Single Ended	No
Wire/Cable Type	Round
Wire Insulation Diameter	N/A
Wire Size (AWG)	28

---

This document was generated on Apr 11, 2026

Obsolete