


D-SUB contact insert - VS-15-ST-DSUB/16-MPT-0,5 - 1688078

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



D-SUB contact insert, shell size 2, with 15 signal contacts, male type of contact, screw connection, straight, for panel mounting frame and sleeve housing with IP67 protection

Your advantages

☒ Screw connection



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 179564
GTIN	4017918179564
Weight per Piece (excluding packing)	18.020 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Mechanical characteristics

Connection method	Screw connection
Overvoltage category	III
AWG solid min.	26
AWG solid max.	20
Degree of pollution	2
Conductor cross section	0.14 mm ² ... 0.5 mm ²
Weight	15.1 g

D-SUB contact insert - VS-15-ST-DSUB/16-MPT-0,5 - 1688078

Technical data

Mechanical characteristics

Flammability rating according to UL 94	V0
--	----

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

Material data

Contact surface material	Au/Ni
Contact material	Copper alloy
Housing material	Steel
Housing surface material	tin-plated
Width	39.3 mm
Height	12.6 mm
Length	48 mm
Mounting type	Hole

Electrical characteristics


Number of positions	15
Rated current	5 A
Overvoltage category	III
Degree of pollution	2
Rated voltage (III/3)	60 V
Insulation resistance	$\geq 5000 \text{ M}\Omega$
Insertion/withdrawal cycles	≤ 200

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Drawings

D-SUB contact insert - VS-15-ST-DSUB/16-MPT-0,5 - 1688078



D-SUB contact insert

Classifications

eCl@ss

eCl@ss 10.0.1	27440205
eCl@ss 11.0	27440223
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440302
eCl@ss 9.0	27440205

ETIM

ETIM 2.0	EC000438
ETIM 3.0	EC000438
ETIM 4.0	EC000438
ETIM 6.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522
UNSPSC 18.0	39121522
UNSPSC 19.0	39121522

D-SUB contact insert - VS-15-ST-DSUB/16-MPT-0,5 - 1688078

Classifications

UNSPSC

UNSPSC 20.0	39121522
UNSPSC 21.0	39121522

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01687
-----	---	---------

Accessories

Accessories

Panel mounting frame

D-SUB panel mounting frames - VS-15-A - 1688036



D-SUB panel mounting frame, shell size 2, IP67 degree of protection

Sleeve housings

D-SUB sleeve housings - VS-15-T-2PG11 - 1688052



D-SUB sleeve housing, shell size 2, IP67 degree of protection

D-SUB contact insert - VS-15-ST-DSUB/16-MPT-0,5 - 1688078

Accessories

Phoenix Contact 2022 © - all rights reserved
<http://www.phoenixcontact.com>