



POS. "n"	L±0.4	PART NO.	
2	4.58	0-829163-2	
3	7.12	0-829163-3	OBSOLETE
4	9.66	0-829163-4	
5	12.20	0-829163-5	
7	17.28	0-829163-7	
8	19.82	0-829163-8	OBSOLETE
10	24.90	1-829163-0	OBSOLETE

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	PART OBSOLESCENCE	26MAR2024	KA	SS



⚠ MATING SIDE: Min 0.76 μ m (PdNi + Au FLASH)IN ZONE "F" OVER Min 1.27 μ m Ni
(Alternative plating – Min 0.76 μ m Au OVER Min 1.27 μ m Ni)
SOLDER SIDE: MIN. 3.0 μ m Sn OVER Min 1.27 μ m Ni

USED FOR E-87-9401		ITEM NO.	DESCRIPTION		MATERIAL	PLATING COLOR	
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN A.HO 21MAR1988	TE Connectivity			
			CHK SCHAARSCHMIDT 21MAR1988				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm		APVD —	NAME AMPMODU II PIN HEADER 90 DEG, SINGLE ROW		
		PRODUCT SPEC 108-18012		—			
		APPLICATION SPEC —					
		WEIGHT —					
		FINISH SEE TABLE					
MATERIAL SEE TABLE		CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO C-829163	RESTRICTED TO —
				SCALE 4:1	SHEET 1 OF 1	REV G2	