

Han 6Ex UL-F-s




Image is for illustration purposes only. Please refer to product description.

Part number	09 36 506 2701
Specification	Han 6Ex UL-F-s
HARTING eCatalogue	https://harting.com/09365062701

Identification

Category	Inserts
Series	Han® Ex

Version

Termination method	Screw termination
Gender	Female
Size	6 B
Number of contacts	6
PE contact	Yes
Details	for US purposes only
Details	ATTENTION! Only to be used with Han® Ex hoods and housings!

Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm ²
Rated current	10 A
Rated voltage	90 V
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤1 mΩ
Tightening torque	0.5 Nm Fixing screws M3 1.2 Nm PE screw M4
Recommended screw driver	Slotted 0.6 x 3.5 Slotted 0.8 x 4.5 PH2
Limiting temperature	-20 ... +40 °C



Pushing Performance
Since 1945

Technical characteristics

Note on the limiting temperature	Up to +70 °C in T4
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 2237 CYJX2.E482115 CSA-C22.2 No. 213 CYJX8.E482115
----------	--

Commercial data

Packaging size	1
Net weight	50.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140186897
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522