






NOTES:

1. MATERIAL:
   HOUSING: LIQUID CRYSTAL POLYMER, BLACK, 30% GLASS FILLED, UL94V-0.
   TERMINAL: BRASS.
   SHELL: STAINLESS STEEL
2. PLATING:
   TERMINAL:
   CONTACT AREA: 0.76 MICROMETER (30 µ") GOLD PLATING
   AND SOLDER TAIL: 1~3 MICROMETER(39~118µ") MATT TIN UNDER PLATE
   UNDER PLATE: 2~4 MICROMETER(79~158µ") NICKEL PLATING OVERALL.
   SHELL: 1.27~2.54 MICROETER(50~100µ") SOLDERABLE NICKEL PLATING OVERALL.
3. SOLDERTAIL COPLANARITY 0.10 MAX.
4. PRODUCT SPEC REFER TO PS-47272-001
5. PACKAGE REFER TO PK-47272-001










RECOMMENDED PCB LAYOUT(THICKNESS=1.6±0.15)

472720121



UNSPECIFICED DIMENSION ARE SAME AS 472720001

PART NO.	COVER	MYLAR	REMARK
472720001	WITHOUT	WITHOUT	SHEET 1
472720024	WITH	WITH	SHEET 2
472720029	WITHOUT	WITH	SHEET 3

DOCUMENT STATUS	P1	RELEASE DATE	2019/10/11 03:37:36

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SYMBOLS: F = 0, E = 0, D = 0, S = 0, ▼ = 0, C = 0, ☒ = 0, ■ = 0, ▽ = 0

DIMENSION UNITS: mm — SCALE: 0.9:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	±	3.0 °
4 PLACES	±	
3 PLACES	±	
2 PLACES	±	0.25
1 PLACE	±	0.25
0 PLACES	±	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 618483
DRWN: RZHANG 2019/09/23
CHK'D: AYIN 2019/10/11
APPR: AYIN 2019/10/11

INITIAL REVISION:
DRWN: RZHANG 2006/04/06
APPR: JNCHEN 2007/03/23

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 47272

molex

1.0MM PITCH DISPLAY PORT
RECEPTACLE ASSEMBLY


PRODUCT CUSTOMER DRAWING


DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-47272-001	PSD	001	D


MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	GENERAL MARKET	1 OF 3


Downloaded from Arrow.com.

WITH COVER AND MYLAR









NOTES:

1.UNSPECIFICED DIMENSION ARE SAME AS SHEET1


2.CONNECTOR WITH COVER IS USED FOR WARE SOLDERING PEG


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
= 0	DIMENSION UNITS: mm	SCALE: 1:1	CURRENT REV DESC:	molex
= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			1.0MM PITCH DISPLAY PORT RECEPTACLE ASSEMBLY
= 0	ANGULAR TOL ± 3.0 °		EC NO: 618483	
= 0	4 PLACES ±		DRWN: RZHANG 2019/09/23	PRODUCT CUSTOMER DRAWING
= 0	3 PLACES ±		CHK'D: AYIN 2019/10/11	
= 0	2 PLACES ± 0.25		APPR: AYIN 2019/10/11	DOCUMENT NUMBER: SD-47272-001 / DOC TYPE: PSD / DOC PART: 001 / REVISION: D
= 0	1 PLACE ± 0.25		INITIAL REVISION:	
= 0	0 PLACES ±		DRWN: RZHANG 2006/04/06	
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APPR: JNCHEN 2007/03/23	
= 0	THIRD ANGLE PROJECTION	DRAWING: A3-SIZE	SERIES: 47272	MATERIAL NUMBER / CUSTOMER: GENERAL MARKET / SHEET NUMBER: 2 OF 3


DOCUMENT STATUS	P1	RELEASE DATE	2019/10/11 03:37:36


Downloaded from Arrow.com.

STANDARD TYPE WITH MYLAR









NOTES:

1. UNSPECAFIC DIMENSION ARE SAME AS SHEET1
2. THE RECOMMENDER PCB ARE SAME AS SHEET1

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
ER = 0	DIMENSION UNITS: mm	SCALE: 1:1	CURRENT REV DESC:	molex
EC = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			1.0MM PITCH DISPLAY PORT RECEPTACLE ASSEMBLY
EP = 0	ANGULAR TOL ± 3.0 °		EC NO: 618483	
S = 0	4 PLACES ±		DRWN: RZHANG 2019/09/23	PRODUCT CUSTOMER DRAWING
▼ = 0	3 PLACES ±		CHK'D: AYIN 2019/10/11	
C = 0	2 PLACES ± 0.25		APPR: AYIN 2019/10/11	DOCUMENT NUMBER: SD-47272-001 / DOC TYPE: PSD / DOC PART: 001 / REVISION: D
☒ = 0	1 PLACE ± 0.25		INITIAL REVISION:	
■ = 0	0 PLACES ±		DRWN: RZHANG 2006/04/06	
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION / DRAWING: A3-SIZE / SERIES: 47272	APPR: JNCHEN 2007/03/23	MATERIAL NUMBER / CUSTOMER: GENERAL MARKET / SHEET NUMBER: 3 OF 3

DOCUMENT STATUS	P1	RELEASE DATE	2019/10/11 03:37:36

Downloaded from Arrow.com.