


MLZ1608N4R7LT000



Applications	Commercial Grade
Feature	No Directivity No Directivity
	Multilayer Multilayer
	Shield Magnetic Shield
	Ferrite Core Ferrite Core
Series Type	MLZ
Status	Production
Brand	TDK



Size	
Length(L)	1.60mm ±0.15mm
Width(W)	0.80mm ±0.15mm
Thickness Height	0.80mm ±0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics	
Inductance	4.7μH ±20% at 2MHz
Rated Current (L Change) [Typ.]	
Rated Current (L Change) [Max.]	80mA (50% Down)
Rated Current (Temperature Rise) [Typ.]	400mA (20°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	320mΩ
DC Resistance [Max.]	416mΩ
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C
Soldering Method	Reflow
	Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel]

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

MLZ1608N4R7LT000









Package Quantity	4000pcs
Weight	0.004g

MLZ1608N4R7LT000




Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)





Associated Images

Shapes and Dimensions



Land Pattern (Terminal Connection)

