





Features:

- Switched-mode power supply
- Natural convection cooling when horizontally mounted
- Stepped profile, ideal for distribution boards/boxes
- Overhead mounting is possible with derating
- Suitable for both parallel and series operation
- Electrically isolated output voltage (SELV) per EN 61010-2-201/UL 60950-1; PELV per EN 60204

Technical data			
Input		Output	
Phases	1	Nominal output voltage $U_{o\,nom}$	DC 5 V (SELV)
Nominal input voltage $U_{i\,nom}$	1 x AC 100 ... 240 V	Output voltage range	DC 4.5 ... 8.5 V (adjustable)
Input voltage range	1 x AC 85 ... 264 V; DC 120 ... 300 V	Default Setting	DC 5 V
Nominal mains frequency range	44 ... 66 Hz; 0 Hz	Nominal output current $I_{o\,nom}$	5.5 A (5 VDC); 3.5 A (in any mounting position)
Input current I_i	≤ 0.29 A (230 VAC); ≤ 0.56 A (110 VAC)	Nominal output power	27.5 W
Discharge current	≤ 1 mA	Deviation	≤ 2 %
Inrush current	≤ 30 A (NTC)	Residual ripple	≤ 100 mV (peak-to-peak)
Power factor correction (PFC)	Passive	Current limitation	$1.1 \times I_{o\,nom}$ (typ.)
Mains failure hold-up time	≥ 80 ms (230 VAC); ≥ 10 ms (110 VAC)	Overload behavior	Constant current



Signaling and communication	
Signaling	1 x Status indication LED (green)
Operation status indicator	Green LED (U _o)

Efficiency/power losses	
Power loss P _I	≤ 2.4 W; ≤ 9.4 W (230 VAC; nominal load)
Power loss (max.) P _{I(max)}	9.9 W (264 VAC / 5 VDC; 5.5 A)
Efficiency (typ.)	75 %

Circuit protection	
Internal fuse	T 2 A / 250 VAC
Backup fusing (required)	An external DC fuse is required for the DC input voltage.
Backup fusing (recommended)	Circuit breaker: 6 A (C characteristic), 10 A (B characteristic) or higher

Safety and protection	
Isolation voltage (pri.-sec.)	DC 4.242 kV
Protection class	II
Protection type	IP20; per EN 60529
Resistance to reverse feed	≤ DC 10 V
Overvoltage category	II
Pollution degree	2
Transient suppression (primary)	Varistor
Overvoltage protection; secondary	≤ 16 VDC (in the event of a fault)
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes
Series operation	Yes
MTBF	> 500,000 h (per IEC 61709)

Connection data	
Connection type 1	Input/output
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 740 Series
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Strip length	6 ... 7 mm / 0.24 ... 0.28 inches

Physical data	
Width	72 mm / 2.835 inches
Height	89 mm / 3.504 inches
Depth	59 mm / 2.323 inches
Depth from upper-edge of DIN-rail	55 mm / 2.165 inches

Mechanical data	
Housing design	DIN-rail-mount enclosure
Mounting type	DIN-35 rail



Material data	
Flammability class per UL94	V0
Fire load	0 MJ
Weight	240 g

Environmental requirements	
Ambient temperature (operation)	-25 ... +60 °C (Device starts at -40 °C (type-tested))
Ambient temperature (storage)	-25 ... +80 °C
Ambient temperature UL (operation at U _N)	-25 ... +55 °C
Relative humidity	5 ... 96 % (no condensation permissible)
Derating	-3 %/K (> 45 °C)
Climatic category	3K3 (per EN 60721)

Standards and specifications	
Conformity marking	CE
Standards/specifications	EN 61010-1 EN 61010-2-201 EN 61204-3 UL 60950-1 UL 508 DNV

Commercial data	
eCl@ss 10.0	27-04-07-01
eCl@ss 9.0	27-04-07-01
ETIM 8.0	EC002540
ETIM 7.0	EC002540
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143098816
Customs tariff number	85044083900

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
  			Approval	Standard	Certificate Name
EAC	TP TC 004/2011	EAC CoC 03078	EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
GZO Almaty Standart					
EAC	TP TC 020/2011	EAC CoC 03081			
GZO Almaty Standart					
UL	UL 508	E255817			
Underwriters Laboratories Inc.					
UR	UL 60950-1	E255815			
Underwriters Laboratories Inc.					



Downloads

Environmental Product Compliance

Compliance Search			
Environmental Product Compliance 787-1020			

Documentation

Bid Text			
787-1020	12.06.2019	docx 20.36 KB	
787-1020	24.06.2019	xml 6.83 KB	

Instruction Leaflet			
Power Supply COM-PACT	29-03-2021 20.12.2021	pdf 2143.15 KB	

CAD/CAE-Data

CAD data	
2D/3D Models 787-1020	

CAE data	
EPLAN Data Portal 787-1020	
WSCAD Universe 787-1020	
ZUKEN Portal 787-1020	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking strip



Item No.: 210-831
Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive; white



Item No.: 210-832
Marking strips; on reel; 3 mm wide; plain; Self-adhesive; white

1.1.2 Tool

1.1.2.1 Operating tool



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured



Item No.: 210-769
SCREWDRIVER; green

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com