



PRODUCT NUMBER	PITCH
VMxx75x200J0G	5.00 mm





N=NUMBER OF POLES

Dim L=(N-1)×5.00+15.0
Dim A=(N-1)×5.00+5.5
Dim B=(N-1)×5.00
Dim C=(N-1)×5.00+10.0
Dim D=N×5.00

POLES	Tolerance
2P-6P	±0.20
7P-12P	±0.25
13P-18P	±0.30
19P-24P	±0.40

PART NO.: VM xx 75 x 2 00J0 G

Solid block	0	Black (RAL9005)	RoHS compliant (lead<4%) In copper Alloy
No. of poles	2	Red (RAL3001/D)	
02 2 poles	3	Orange(RAL2011/P)	
03 3 poles	4	Yellow(RAL1018/A)	
...	5	Green(RAL6018/T)	
24 24 poles	6	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	



Material:

- Item a Clamp: Steel zinc plated.
 - Item b Terminal screw: Steel Zinc plating "-" slot type
 - Item c Female contact: High conductivity copper Tin plated
 - Item d With flange screw: Steel zinc plated M2.5 "-" slot type
 - Item e Terminal (top body): Thermoplastic (UL94V-0)
 - Item f Terminal (bottom body): Thermoplastic (UL94V-0)
 - Item g Clampage: Steel Zinc plated
- Electrical cULus/TUV
- Voltage rating: 300VAC/300VAC
 - Current rating: 20A/20A
 - Wire range: 0.34-2.5mm²
 - Solid wire(AWG): 12-22
 - Stranded wire(AWG): 12-22
 - Torque: 3.5Lb-In / 0.4Nm
 - Screw: M2.5
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV/2.5KV
 - Operating temperature: -40°C to +115°C
 - Safety approval: cULus TUV

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family		
ltr	ecn	no	dr	date	tolerances unless otherwise specified	angles	TERMINAL BLOCK		
					0.5	0.5	TERMINAL BLOCK		
					1	1	PLUGGABLE PLUG, WITH FLANGE		
dr					EVIN ZHONG	041914	FCI		
enr					EVIN ZHONG	041914	dwg no		
chr					HANKE FENG	041914	sheet 1 of 1		
appd					SHI JUN	041914	size		
sheet index	revision	A					type		
	sheet	1					CUSTOMER Drawing		