





APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Nylon46, rated UL 94V-0
Insulator color: White
Contacts: Brass
Plating:
Tin over Copper underplate overall
Electrical:
Operating voltage: 100 VAC max
Current rating: 2 Amps max
Contact resistance: 10 mohms max
Dielectric withstanding voltage: 800 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Halogen & Lead free, RoHS compliant

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/7/05	
A		REVISED DIM.	3/2/12	

Positions: 2 thru 16
A = .079 [2.00] x No. of Positions + .153 [3.90]
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES

X .X ± .10 ØX ± .10
XX .XX ± .020 ØXX ± .015
XXX .XXX ± .015 ØXXX ± .010

APPROVALS
DATE

DRAWN SS 4/7/05

CHECKED

APPROVED

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.079 [2.00] SHROUDED HEADER,
VERTICAL, SURFACE MOUNT

SIZE PART NO. 2SH-C-X*-TS-SMT

REF: S00123T SCALE: NTS SHEET 1 OF 1