



Pushing Performance  
Since 1945

# HanPP V14 RJ45 GL Cat6A plug 8p




Image is for illustration purposes only. Please refer to product description.

Part number	09 35 227 0421
Specification	HanPP V14 RJ45 GL Cat6A plug 8p
HARTING eCatalogue	<a href="https://harting.com/09352270421">https://harting.com/09352270421</a>

## Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	RJ45
Element	Connector sets
Features	Intuitive locking mechanism

## Version

Termination method	Piercing termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Locking type	PushPull
Pack contents	incl. housing and male insert

## Technical characteristics

Conductor cross-section	0.1 ... 0.22 mm² Stranded
	0.26 ... 0.32 mm² Solid
Conductor cross-section [AWG]	AWG 28/7 ... AWG 24/7 Stranded
Wire outer diameter	≤1.05 mm
Rated current	1.75 A
Rated voltage	50 V
Transmission characteristics	Cat. 6 <sub>A</sub> Class E <sub>A</sub> up to 500 MHz



**Pushing Performance**  
Since 1945

## Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65
	IP67
Clamping range	6.5 ... 9.5 mm

## Material properties

Surface (contacts)	Au over Ni Mating side
	Sn over Ni Termination side
Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material (O-ring)	NBR
Material (cable seal)	TPE
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

## Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14)
	IEC 60603-7 Mating face
	EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL

Page 2 / 3 | Creation date 2025-04-16 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97200 | [electronics@HARTING.com](mailto:electronics@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)



Pushing Performance  
Since 1945

Specifications and approvals

PROFINET Yes

Commercial data

Packaging size	10
Net weight	22.14 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140054127
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408