


202K153-3-01/86-0 Product Details

 [Share](#) [Print](#) [Email](#)

202K153-3-01/86-0

TE Internal Number: 502945-000

 [Active](#)

Molded Parts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Molded Part Type = Molded Boot
- Family Name = 202K1
- Straight
- General Purpose Application
- Entry Size, Braided or Magneform Adapter = 12, 13, 14, 15

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Boot, straight with lip](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Molded Part Type](#) = Molded Boot
- Angle = Straight
- Size = 53
- Material = Semi rigid Modified Polyolefin

Body Features:

- Cable Diameter Range (mm [in]) = 8.40 - 19.00 [0.331 - 0.748]

Contact Features:

- [Family Name](#) = 202K1
- Entry Size, Braided or Magneform Adapter = 12, 13, 14, 15

Housing Features:

- Entry Size, Tinel-Lock Adapter = 10, 12, 14
- Entry Size - Solid or Fixed Adapter = 8
- Entry Size - Spin Coupling Adapter = 12
- Adapter Entry Size Outside Diameter (Min-Max) (mm [in]) = 22.40 - 30.00 [0.882 - 1.181]
- [Material Systems Code](#) = 10
- Adhesive Pre-Coating = With
- Adhesive Description = High Performance Pre-Coat Adhesive

Configuration Features:

- Material Code = 3
- Adhesive Code = 86

Industry Standards:

- Government/Industry Qualification = No
- Approved Standards = DEF Std 59-97 Issue 3 Type DA, MIL-I-81765/1 Class I, UL224 E85831
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Operating Temperature (°C) = -55 - +120

Operation/Application:

- Application = General Purpose

Other:

- Brand = Raychem
- Comment = Contact Raychem for additional adhesive and/or cut off boot length information

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

