




SECTION TERMINAISON CONTACT



PC card drilling dimensions(after plating) _____
(thickness 1.60±0.20mm)



LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PV00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PV00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PV00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PV00LF

Plating: 4 ---> flash AU
Plating: 6 ---> 0.76» AU

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PV00
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PV00
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PV00
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PV00

Plating: 4 ---> flash AU
Plating: 6 ---> 0.76» AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

rev	ecn no	dr	date
C	-	JAR	2002/09/10
D	LS05-001	MPE	2005/03/09
E	LS05-0056	MPE	2005/06/27
F	LS06-0097	LGO	2006/07/29
G	109-0268	NG	2009-11-24
-	-	-	-

www.fciconnect.com

FCI

MALE CONNECTOR DELTA D ST

straight,solder type for

catalog no

surface ISO 1302

tolerance std ISO 406 ISO 1101

projection

mm

Scale

2

ECN

109-0268

Rev.

G

Dr

Eng

Chr

Appr

LELEON

PESSON

NIRMAL GEORGE

SUDHIR VARMA

1992-09-14

1992-09-14

2009-11-24

2009-11-24

ANGULAR

LINEAR

Product family

D-SUB

Spec ref

-

tolerances unless otherwise specified

0.X

0.XX

0.XXX

±0.1

±0.1

±0.1

European Views

