

Specification Sheet

Part Number: CTT20R0HSC2



Heat stabilized cable ties provide excellent resistance to high heat exposures.
Head design contains clamping rails to provide full circumferential compression around bundles.
Bent tail allows for quick insertion into head.

Clamp Tie, 4" Long, 20lb Tensile Strength, PA66HS, Black, 100/pkg

Article Number	112-51905
Type	CTT20R
Color	Black (BK)
Quantity Per	bag
Product Description	The 360 degree compression ties are designed with underside clamping rails to allow for optimal surface contact and complete circumferential compression around the bundle. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Clamp Tie, 4" Long, 20lb Tensile Strength, PA66HS, Black, 100/pkg

Global Part Name	CTT20R-PA66HS-BK
------------------	------------------

Minimum Tensile Strength (Imperial)	20.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	90.0
-----------------------------------	------

Length L (Imperial)	4.0
---------------------	-----

Length L (Metric)	101.6
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.1
--------------------	-----

Width W (Metric)	2.5
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	0.51
--------------------------------	------

Bundle Diameter Max (Metric)	13.0
------------------------------	------

Thickness T (Imperial)	0.043
------------------------	-------

Thickness T (Metric)	1.1
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
ROHS Compliant	Yes
Certification/Specification	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

