


This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.



The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
A	NE-16275	TO PRODUCTION	12/05/2016	Roger Tsai





ORIGINAL



P/N: G880 XX 2 X X C1HR
 NO. OF POS. _____
 CONTACT FINISH
 1. 100μ" MATTE TIN
 COLOR
 1. BLACK
 2. NATURAL
 PACKING
 1. TAPE & REEL



MATED CONNECTOR



RECOMMENDED PCB LAYOUT
 ALL TOLERANCE ARE ±0.05

NOTES:

- INSULATOR: HIGH TEMPERATURE THERMAL PLASTIC, NYLON 6T, UL 94V-0, COLOR: OPTION.
- CONTACT: COPPER ALLOY, SELECTIVE PLATING ON CONTACT AREA, 100μ" MIN. MATTE TIN OR GOLD FLASH PLATING ON SOLDERING AREA, UNDER 50μ" MIN. NICKEL UNDER-PLATING OVERALL.
- THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS MATERIAL PER DIRECTIVE 2011/65/EU FOR RoHS.
- PACKING MUST BE PER Amphenol PACKING SPECIFICATION PKS-0001
- PRODUCT SPECIFICATION REFER TO : PS-7582.
- TEST SUMMARY REFER TO : TS-7582-002.

G880 07 2XXX C1HR	7	12.10	7.50	11.00	5.3
G880 06 2XXX C1HR	6	10.85	6.25	9.75	5.3
G880 05 2XXX C1HR	5	9.60	5.00	8.50	5.3
G880 04 2XXX C1HR	4	8.35	3.75	7.25	5.3
G880 03 2XXX C1HR	3	7.10	2.50	6.00	5.3
G880 02 2XXX C1HR	2	5.85	1.25	4.75	5.3
PART NUMBER	NO. OF POSITIONS	DIMENSIONS			
		A	B	C	D

TOLERANCE	APPROVALS	DATE	TITLE		Amphenol®	
X. X.X X.XX X.XXX ANGULAR ±1° UNLESS OTHERWISE SPECIFIED	DRAWN Aqua Chou CHECKED Roger Tsai APPROVED Roger Tsai DWG TYPE CUST DWG	12/05/2016 12/05/2016 12/05/2016	G880 SERIES, WTB CONN 1.25 PITCH, R/A SMT TYPE		Amphenol Corporation Amphenol Taiwan Corporation	
			UNIT mm	SCALE NA	PART No. G880XX2XXXC1HR	REV. A
			SIZE A3	SHEET 1 OF 2	DWG No. G880XX2XXXC1HR	


This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

ORIGINAL



REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
A	NE-16275	TO PRODUCTION	12/05/2016	Roger Tsai



Pos.	W	PCS/Reel	PCS/Carton	Net (Kg)	Gross (Kg)
2	16.0	900	8100	1.28	5.02
3		900	5400	1.02	4.38
4		900	5400	1.15	4.51
5	24.0	900	5400	1.31	4.67
6		900	5400	1.47	4.83
7		900	5400	1.63	4.99

TOLERANCE		APPROVALS		DATE	TITLE				Amphenol® Amphenol Corporation Amphenol Taiwan Corporation			
X.		DRAWN	Aqua Chou	12/05/2016	G880 SERIES, WTB CONN 1.25 PITCH, R/A SMT TYPE							
X.X	±0.30	CHECKED	Roger Tsai	12/05/2016								
X.XX	±0.20											
X.XXX	±0.10	APPROVED	Roger Tsai	12/05/2016			UNIT	mm	SIZE	A3	PART No. G880XX2XXXC1HR	
ANGULAR ±1°		DWG TYPE	CUST DWG	PROJECT CODE			PHD	SCALE	NA	SHEET	2 OF 2	DWG No. G880XX2XXXC1HR
UNLESS OTHERWISE SPECIFIED												