



PRODUCT NUMBER
10075664-001LF









SCALE 1.500

rev	ecn no	dr	date
A	DG07-0073	BF	04/10/2007

www.fciconnect.com			surface	tolerance std ASME Y14.5		projection	MM
			TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	KENNY TAI	01-10-2007	ANGULAR	LINEAR	0.X ±0.50	size A4	Scale 1.000
Eng	KENNY TAI	01-10-2007			0.XX ±.25		
Chr	PAUL WANG	01-10-2007	0° ±2°		0.XXX ±	ECN	DG07-0073
Appr	JOSEPH HSIA	01-10-2007	Product family			Spec ref	*


title	PRESS FIT TYPE POWER EDGE CONNECTOR	dwg no	10075664-001	Rev. A
catalog no	10075664	CUSTOMER		sheet 1 of 2

Copyright FCI.

REV F : 2006-04-17


Downloaded from Arrow.com.

PDM: Rev:A STATUS: Released Printed: Jan 23, 2008



RECOMMENDED PCB LAYOUT
PCB THICKNESS: 3.18mm

SCALE 1.500



RECOMMENDED MATING PCB

CONNECTOR NOTE:
1. HOUSING MATERIAL: HIGH TEMPERATURE THERMOPLASTIC
   UL 94V-0, FLAME RETARDANT.
2. TERMINAL: COPPER ALLOY.
3. PLATING:
   Ni: 50 u"/1.27um UNDERPLATED.
   Au: 30 u"/0.76um ON CONTACT AREA (ONE SIDE).
   Sn: 50 u"/1.27um ON PRESS FIT TAIL.
4. MANUFACTURING CODE PLEASE REFERENCE FCI SPECIFICAITON GS-24-007.

PCB NOTE:
5. ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION OF 0.1mm.
6. ALL DIAMETERS ARE FINISHED HOLE SIZES.
7. Ø1.15mm DRILLED HOLES, PLATED WITH 0.007mm MIN. HASL-FREE Pb.
   OVER 1.03mm TO 0.08mm Cu PLATING TO ACHIEVE A 1.02±0.07mm HOLE.

title: PRESS FIT TYPE POWER EDGE CONNECTOR		dwg no: 10075664-001	Rev. A
catalog no: 10075664		CUSTOMER	sheet 2 of 2

REV F : 2006-04-17

Copyright FCI.

Downloaded from Arrow.com.

PDM: Rev:A STATUS: Released Printed: Jan 23, 2008