
Part Number : 782291033
Product Description : GbX I-Trac Right-Angle Header with Left Hold Down, Power Module, 2 Blades, 40 Amps, 2 Ganged Modules, Lead-Free
Series Number : 78229
Status : Active
Product Category : Backplane Connectors



Documents and Resources

Drawings

782291033_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-78231-007-001.pdf

PS-78231-006-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	78229
Description	GbX I-Trac Right-Angle Header with Left Hold Down, Power Module, 2 Blades, 40 Amps, 2 Ganged Modules, Lead-Free
Application	Daughtercard
Component Type	Power Header
Product Name	GbX I-Trac
UPC	883906023362

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	40.0A
Data Rate	12.0 Gbps
Shielded	No
Shield Type	N/A
Voltage - Maximum	250V DC

Downloaded from Arrow.com.

Physical

Circuits Detail	40 Amps (20/Split Blade) Power Module 1 Blade Length P1, 6.77mm; P2, 9.77mm Power Module 2 Blade Length P1, 6.77mm; P2, 9.77mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	Yes
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	9.782/g
Number of Columns	1
Number of Pairs	4
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.41mm
Pitch - Mating Interface	2.00mm, 7.40mm
Pitch - Termination Interface	2.00mm, 7.40mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-20° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Downloaded from Arrow.com.

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
GbX I-Trac Vertical Receptacles	78227

Use with Part(s)

Description	Part Number
GbX I-Trac Right-Angle Receptacle Modules	76020

Application Tooling

This document was generated on May 21, 2026

Downloaded from Arrow.com.