




SERIES: SR5 | DESCRIPTION: SIGNAL RELAY

FEATURES

- 3~24 Vdc coil voltage
- 200 mW coil power
- contact form 1C




MODEL

	coil voltage typ (Vdc)	coil resistance  ( $\Omega \pm 10\%$ )	operating voltage  min (Vdc)	release voltage max (Vdc)	coil power typ (mW)
SR5-3V-200-1C	3	45	2.25	0.3	200
SR5-5V-200-1C	5	125	3.75	0.5	200
SR5-9V-200-1C	9	405	6.75	0.9	200
SR5-12V-200-1C	12	720	9.0	1.2	200
SR5-24V-200-1C	24	2,880	18.0	2.4	200

Notes: 1. All specifications are measured at 23°C unless otherwise specified.

PART NUMBER KEY



CONTACT SPECIFICATIONS


parameter	conditions/description	min	typ	max	units
contact form	1 Form C				
contact material	AuAg overlay				
contact rating	1 A @ 120 Vac, 24 Vdc				
contact resistance	at 6 Vdc, 0.1 A			50	mΩ
max switching voltage				220	Vac
				30	Vdc
max switching current				3	A
max switching power				360	VA
				72	W
min switching load	5 Vdc, 10 mA				
life	electrical		100,000		operations
	mechanical		10,000,000		operations

GENERAL SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
insulation resistance	at 500 Vdc	100			MΩ
dielectric strength	between open contacts for 1 minute		750		Vac
	between coil and contacts for 1 minute		1,000		Vac
operate time				5	ms
release time				5	ms
shock resistance	endurance		1,000		m/s <sup>2</sup>
	misoperation		100		m/s <sup>2</sup>
vibration resistance	endurance: 10~55 Hz, 1.5 mm double amplitude				
	misoperation: 10~55 Hz, 1.5 mm double amplitude				
operating temperature		-25		70	°C
humidity	at 40°C	35		95	%RH
weight			4.0		g
safety approvals	UL/cUL 508				
flammability rating	UL94V-0				
RoHS	yes				
packaging	tube: 25 pcs per tube				
	carton size: 466 x 306 x 140 mm				
	carton QTY: 2,000 pcs per carton				

SOLDERABILITY


parameter	conditions/description	min	typ	max	units
hand soldering	for 3.5±0.5 seconds	340	350	360	°C
wave soldering	for 10±1 seconds	255	260	265	°C





Double-wave Soldering Curve

MECHANICAL DRAWING


units: mm  
tolerance:  $\pm 0.3$  mm  
unless otherwise noted



ITEM	DESCRIPTION	MATERIAL	PLATING/COLOR
A	housing	PBT [UL94V-0]	orange
B	terminals	copper covered steel	tin




Recommended PCB Layout  
Bottom View




Wiring Diagram  
Bottom View

## CHARACTERISTIC CURVES


Time Curve




Coil Temperature Rise




Operate Range



Life Curve



Maximum Switching Power



REVISION HISTORY

rev.	description	date
1.0	initial release	06/08/2022
1.01	logo, datasheet style update	10/27/2022
1.02	CUI Devices rebranded to Same Sky	09/12/2024

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**