



POSITRONIC INDUSTRIES BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC INDUSTRIES ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

SK2392

DATE	REV	REVISION RECORD	APP	DR	CK
6-19 06	A	ECO 26200		YK	



NOTES:

- ## 1. MATERIALS AND FINISHES:

INSULATOR: GLASS FILLED DAP PER ASTM-D-5948 TYPE SDG-F, COLOR, GREY.

CONTACTS: COPPER ALLOY, 0.000015 [0.38μ] GOLD OVER NICKEL PLATE.

JACKSCREWS: STAINLESS STEEL PASSIVATED.

- ## 2. ELECTRICAL CHARACTERISTICS:

CONTACT CURRENT RATING: 5 AMPS.


INITIAL CONTACT RESISTANCE: 0.012 OHMS.

INSULATOR RESISTANCE: 5 G OHMS.


WORKING VOLTAGE: 250 V.AC (rms)

3. TEMPERATURE RANGE: -55°C TO +135°C.

4. DIMENSIONS ARE IN INCHES [MILLIMETERS].



POSITRONIC
INDUSTRIES INC.
www.connectpositronic.com



DECIMAL TOL.
± 0.015 [0.38]

SGM SERIES

SCALE
N.T.S.

DRAWN BY	YK
APPROVED BY	

TITLE

SGM7MSCESS0000

ANGULAR TOL.
 $\pm 5^{\circ}$

DATE
6-19-06

DRAWING NUMBER	SK2392
----------------	--------

REV.
A