






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	04/26/16	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:
 Insulator: Hi-temp Thermoplastic, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass

Plating:
 Matte Tin over Nickel underplate overall.

Electrical:
 Operating voltage: 250 VAC max
 Current rating: 3 Amps max
 Contact resistance: 20 mohms max
 Insulation resistance: 1000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1500 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -250°C to +85°C
 Environmental:
 Lead free, RoHS compliant.



Positions: 03 thru 12
 A= .100 [2.54] x No. of Position + .100 [2.55]
 B= .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DATE			.100 [2.54] LATCHING HEADER, STRAIGHT PCB MOUNT, MATTE TIN, HI-TEMP		
DRAWN	TW	04/26/16	SIZE	PART NO.	REV.
CHECKED			X	CDR-XX-MTS-P1-HT	-
APPROVED			REF:	S00186T	SCALE: NTS
			SHEET 1 OF 1		