




**Part Number :** [5601230701](#)  
**Product Description :** DuraClik ISL Wire-to-Board  
Receptacle Housing, Single Row, Black, 7 Circuits  
**Series Number :** 560123  
**Status :** Active  
**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[5601230701\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-560123-001-001.pdf](#)

[PK-560123-001-001.pdf](#)

[PS-560123-001-001.pdf](#) (Tin Plating)

[PS-560123-003-001.pdf](#) (Tin Plating)

[5601240131-000.pdf](#) (Gold Plating)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	560123
Description	DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, Black, 7 Circuits
Application	Automotive, Signal, Wire-to-Board
Product Name	DuraClik
UPC	191130507122

### Agency

UL	E29179
----	--------

### Physical

Circuits (maximum)	7
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes

Material - Resin	PBT
Net Weight	0.414/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +130°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
DuraClik Right-Angle Single Row Headers	<u>502352</u>
DuraClik Vertical Single Row Headers	<u>560020</u>

### Use with Part(s)

Description	Part Number
DuraClik Wire-to-Board Independent Secondary Lock (ISL) Retainer, 7 Circuits, Gray	<u>5601250700</u>
DuraClik ISL Female Crimp Terminals	<u>560124</u>

---

This document was generated on Sep 14, 2025