

62827-1 ✓ ACTIVE

TE Internal #: 62827-1


Quick Disconnect Tab, Uninsulated, 23 – 22 AWG, .26 – .33 mm²

Wire, Straight, Stainless Steel, Unplated Plating, Strip/Reel, Open Barrel

[View on TE.com >](#)



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.26 – .33 mm²**

Terminal Orientation: **Straight**

Contact Base Material: **Stainless Steel**

Features

Configuration Features

Compatible With Wire & Cable Type

Discrete Wire

Contact Features

Quick Disconnect Terminal Type

Tab

Terminal Orientation

Straight

Contact Base Material

Stainless Steel

Terminal Plating Material

Unplated

Barrel Type

Open

Termination Features

Product Terminates To

Wire & Cable

Mechanical Attachment

Wire Insulation Support

Without

Dimensions

Product Length

15.24 mm[.6 in]

Terminal Material Thickness

.2 mm[.008 in]

Wire Size

.26 – .33 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Packaging Features

Packaging Quantity	10000
Packaging Method	Strip/Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





Documents

Product Drawings

[WELD TAB 24-22 AWG SST](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_62827-1_K.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62827-1_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62827-1_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.