

Network cable - VS-OE-OE-94A-100,0 - 1416305

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Network cable, Ethernet CAT5 (1 Gbps), 8-position, PUR, water blue RAL 5021, shielded, free cable end, on free cable end, cable length: 100 m



Ethernet

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 473545
GTIN	4046356473545
Weight per Piece (excluding packing)	5,500.000 g
Custom tariff number	85444290
Country of origin	Germany

Technical data

Dimensions

Length of cable	100 m
-----------------	-------

General data

Number of positions	8
Signal type/category	Ethernet CAT5 (IEC 11801), 1 Gbps
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps

Cable

Cable type	Ethernet
Cable type (abbreviation)	94A
UL AWM style	20549 (80°C/300 V)

Network cable - VS-OE-OE-94A-100,0 - 1416305

Technical data

Cable

Signal type/category	Ethernet CAT5 (IEC 11801), 1 Gbps
Cable structure	4x2xAWG24/1; SF/UTP
Conductor cross section	4x 2x 0.25 mm ²
AWG signal line	24
Conductor structure signal line	1x 0.50 mm
Core diameter including insulation	1.1 mm ±0.05 mm
Wire colors	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Twisted pairs	2 cores to the pair
Overall twist	4 pairs for core
Shielding	Aluminum-lined polyester foil, tinned copper braided shield
Optical shield covering	85 %
External sheath, color	water blue RAL 5021
Outer sheath thickness	0.4 mm
External cable diameter D	6.4 mm ±0.2 mm
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm (for installation)
Tensile strength GRP	80 N
Outer sheath, material	PUR
Material conductor insulation	PE
Conductor material	Bare Cu wire
Insulation resistance	≥ 5 GΩ*km
Conductor resistance	< 93.8 Ω/km
Cable capacity	< 56 nF/km
	< 1600 pF/km (Pair-Ground)
Signal speed	0.6 c
Signal runtime	5.7 ns/m
Nominal voltage, cable	72 V DC
	300 V AC (in acc. with UL)
Test voltage Core/Core	2500 V DC
Flame resistance	According to FT-2
Halogen-free	According to IEC 60754-2
Resistance to oil	according to IEC 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (installation)	0 °C ... 50 °C
Shielded	yes

Environmental Product Compliance

Network cable - VS-OE-OE-94A-100,0 - 1416305


Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Cable cross section



Ethernet [94A]

Classifications

eCl@ss

eCl@ss 10.0.1	27060390
eCl@ss 11.0	27061801

Network cable - VS-OE-OE-94A-100,0 - 1416305

Classifications

eCl@ss

eCl@ss 4.0	24010400
eCl@ss 4.1	24010400
eCl@ss 5.0	19030300
eCl@ss 5.1	19030300
eCl@ss 6.0	27061800
eCl@ss 7.0	27061801
eCl@ss 9.0	27061801

ETIM

ETIM 3.0	EC000830
ETIM 4.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC000748

UNSPSC

UNSPSC 6.01	26121616
UNSPSC 7.0901	26121616
UNSPSC 11	26121604
UNSPSC 12.01	31261501
UNSPSC 13.2	26121604
UNSPSC 18.0	26121604
UNSPSC 19.0	26121604
UNSPSC 20.0	26121604
UNSPSC 21.0	26121604

Approvals

Approvals

Approvals

EAC-RoHS

Ex Approvals

Approval details

Network cable - VS-OE-OE-94A-100,0 - 1416305

Approvals

EAC-RoHS



RU D-
DE.HB35.B.00385

Accessories

Accessories

Stripping tool - VS-CABLE-STRIP-VARIO - 1657407



Stripping tool, for the multi-level stripping of shielded cables