

$71,7 \pm 0,1$

component side 1

all holes

$\oplus$	$\phi 0,05$	J	L
----------	-------------	---	---

$\varnothing 0,55 \pm 0,05$ 

0,75

2,15

3,35

2,64

26,1

$$84 \times 0,75 (=63)$$

4 x

	$\varnothing 0$
---	-----------------

05	J	L
----	---	---

$$\phi 1,8 \pm$$

0,03 

1,76 max.

2x

	$\varnothing 0,04$	L	J
---	--------------------	---	---

9,87 ± 0,03

 $6,74 \pm 0,02$ $(10:1)$

① *plated holes*

2 *non-metallized drillings*

*mating steps acc. to
PICMG MicroTCA.0 and AdvancedMC.0*

The following 54 contacts are internally connected
(ground pins acc. to AdvancedMC.0): 7, 10, 13, 16, 19, 22, 25, 28,
31, 34, 37, 40, 43, 46, 49, 52, 55, 58, 61, 64, 67, 70, 73, 76, 79,
82, 85, 86, 89, 92, 95, 98, 101, 104, 107, 110, 113, 116, 119, 122,
125, 128, 131, 134, 137, 140, 143, 146, 149, 152, 155, 158, 161, 16

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maße/Free size tolerances					
.	.	.		Dat.	Name	Maßstab/Scale 2:1	Piggyback, Plug-Connector Basic Side, 170 pole solder							
.	.	.	Detail.	2014-10-17	LoWi									
.	.	.	Insp.	.	.									
.	.	.	Stand.	.	.									
.	.	.	 ITB Advanced Connectors					TB 16 25 170 1301 000			Blatt/ page 1 / 1			
.	.	.						Mod.		Dat.	Name	Sub.		