





PRODUCT NUMBER	PITCH
YK44Axx0x0J0G	9.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT: 300V 25A
 WITHSTAND VOLTAGE: AC2000V/min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 10.54 Lb-In
 WIRE RANGE: 22-12 AWG
 1) HOUSING: Thermoplastic, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M3.5

DIMENSION

Dim A	N×9.5±1.5
Dim B	(N-1)×9.5

N=Number of poles

Poles	Tolerance
2p-4p	±0.20
5p-8p	±0.25
9p-16p	±0.35
17p-23p	±0.40
24p-30p	±0.50

PART NO.: YK 44Axx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles

 30 30 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK										
ltr	ecn no		dr	date	tolerances unless otherwise specified						title TERMINAL BLOCK									
					angles		linear	X.±0.5			BARRIER TYPE									
								X.X±0.3												
					X*±1"			X.XX±0.1												
					dr	EVAN LU		061614			dwg no				sheet 1 of 1				size	
					enrg	EVAN LU		061614			YK44Axx0x0J0G				A4					
					chr	HANKE FENG		061614			CUSTOMER Drawing									
					appd	SHI JUN		061614												
sheet index		revision sheet		A 1																