





Rev	AWO #	Description	Date	Appr
-		RELEASED	6/11/12	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over copper underplate overall.

Electrical:

Voltage Rating: 250V AC

Current Rating: 3 Amps Max

Contact resistance: 15 mohms max. initial

Insulation resistance: 1500 Mohms min.

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Temperature Range: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 20
A = .098 [2.50] x No. of Spaces
B = .098 [2.50] x No. of Positions

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.098 [2.50] PITCH WAFER, VERTICAL

PCB TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]				ADAM TECH			
TOLERANCES: EXCEPT AS NOTED				909 Railway Avenue, Union, NJ 07083			
INCHES				Phone: 908-687-5000 Fax: 908-687-5710			
HOLES				TITLE			
.X	± .10	Ø.X	± .10	.098 [2.50] PITCH WAFER, VERTICAL			
.XX	± .020	Ø.XX	± .015	PCB TYPE			
.XXX	± .015	Ø.XXX	± .010	SIZE			
APPROVALS				PART NO.			
DATE				25SH-M-XX-TS			
DRAWN	AY	6/11/12		REV.			
CHECKED	AH	6/11/12		-			
APPROVED				REF: S00124T SCALE: NTS SHEET 1 OF 1			