

PrimePACK™2 module with TRENCHSTOP™ IGBT7 and emitter controlled 7 diode and NTC

Features

- Electrical features
 - $V_{CES} = 1200\text{ V}$
 - $I_{C\text{ nom}} = 1600\text{ A} / I_{CRM} = 3200\text{ A}$
 - Extended operating temperature $T_{vj\text{ op}}$
 - Low $V_{CE,sat}$
- Mechanical features
 - 4 kV AC 1 min insulation
 - High creepage and clearance distances
 - High power and thermal cycling capability
 - High power density



Potential applications

- Motor drives
- Construction, commercial, and agriculture vehicles
- UPS systems
- Energy storage systems

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	3
3	Diode, Inverter	5
4	NTC-Thermistor	6
5	Characteristics diagrams	7
6	Circuit diagram	11
7	Package outlines	12
8	Module label code	13
	Revision history	14
	Disclaimer	15

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 60 \text{ s}$	4.0	kV
Material of module baseplate			Cu	
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Creepage distance	d_{Creep}	terminal to heatsink	33.0	mm
Creepage distance	d_{Creep}	terminal to terminal	33.0	mm
Clearance	d_{Clear}	terminal to heatsink	19.0	mm
Clearance	d_{Clear}	terminal to terminal	19.0	mm
Comparative tracking index	CTI		> 400	

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	L_{SCE}			18		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_C = 25^\circ\text{C}$, per switch		0.22		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_C = 25^\circ\text{C}$, per switch		0.3		mΩ
Storage temperature	T_{stg}		-40		150	°C
Mounting torque for module mounting	M	- Mounting according to valid application note	M5, Screw	3	6	Nm
Terminal connection torque	M	- Mounting according to valid application note	M4, Screw	1.8	2.1	Nm
			M8, Screw	8	10	
Weight	G			825		g

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = 25^\circ\text{C}$	1200	V
Implemented collector current	I_{CN}			1600	A
Continuous DC collector current	I_{CDC}	$T_{vj \text{ max}} = 175^\circ\text{C}$	$T_C = 90^\circ\text{C}$	1600	A

(table continues...)

Table 3 (continued) Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\ op}$	3200	A
Gate-emitter peak voltage	V_{GES}		± 20	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 1600\ A, V_{GE} = 15\ V$	$T_{vj} = 25\ ^\circ C$	1.27	1.79	V
			$T_{vj} = 125\ ^\circ C$	1.37	1.82	
			$T_{vj} = 175\ ^\circ C$	1.43	1.85	
Gate threshold voltage	V_{GEth}	$I_C = 32\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$	5.15	5.80	6.45	V
Gate charge	Q_G	$V_{GE} = \pm 15\ V, V_{CC} = 600\ V$		25.4		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\ ^\circ C$		0.5		Ω
Input capacitance	C_{ies}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$		217		nF
Reverse transfer capacitance	C_{res}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$		1.28		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1200\ V, V_{GE} = 0\ V$	$T_{vj} = 25\ ^\circ C$		5	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$			400	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 1600\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.35\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.700		μs
			$T_{vj} = 125\ ^\circ C$	0.800		
			$T_{vj} = 175\ ^\circ C$	0.870		
Rise time (inductive load)	t_r	$I_C = 1600\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.35\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.130		μs
			$T_{vj} = 125\ ^\circ C$	0.150		
			$T_{vj} = 175\ ^\circ C$	0.160		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 1600\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Goff} = 1\ \Omega$	$T_{vj} = 25\ ^\circ C$	1.050		μs
			$T_{vj} = 125\ ^\circ C$	1.150		
			$T_{vj} = 175\ ^\circ C$	1.250		
Fall time (inductive load)	t_f	$I_C = 1600\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Goff} = 1\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.200		μs
			$T_{vj} = 125\ ^\circ C$	0.400		
			$T_{vj} = 175\ ^\circ C$	0.500		
Turn-on energy loss per pulse	E_{on}	$I_C = 1600\ A, V_{CC} = 600\ V, L_\sigma = 30\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 0.35\ \Omega, di/dt = 9350\ A/\mu s (T_{vj} = 175\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$	125		mJ
			$T_{vj} = 125\ ^\circ C$	225		
			$T_{vj} = 175\ ^\circ C$	290		

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Turn-off energy loss per pulse	E_{off}	$I_C = 1600\text{ A}$, $V_{CC} = 600\text{ V}$, $L_\sigma = 30\text{ nH}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 1\text{ }\Omega$, $dv/dt = 2100\text{ V}/\mu\text{s}$ ($T_{vj} = 175\text{ }^\circ\text{C}$)	$T_{vj} = 25\text{ }^\circ\text{C}$	260		mJ
			$T_{vj} = 125\text{ }^\circ\text{C}$	360		
			$T_{vj} = 175\text{ }^\circ\text{C}$	410		
SC data	I_{SC}	$V_{GE} \leq 15\text{ V}$, $V_{CC} = 800\text{ V}$, $V_{CEmax} = V_{CES} - L_{sCE} \cdot di/dt$	$t_p \leq 6\text{ }\mu\text{s}$, $T_{vj} \leq 150\text{ }^\circ\text{C}$	5300		A
			$t_p \leq 6\text{ }\mu\text{s}$, $T_{vj} \leq 175\text{ }^\circ\text{C}$	5100		
Thermal resistance, junction to case	R_{thJC}	per IGBT			27.4	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per IGBT		20.6		K/kW
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	$^\circ\text{C}$

Note: Maximum RMS module DC-terminal current according to application note AN2009-08.

$T_{vj\text{ op}} > 150\text{ }^\circ\text{C}$ is only allowed for operation at overload conditions. For detailed specifications please refer to AN2018-14.

3 Diode, Inverter

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = 25\text{ }^{\circ}\text{C}$	1200	V
Continuous DC forward current	I_F			1600	A
Repetitive peak forward current	I_{FRM}	$t_P = 1\text{ ms}$		3200	A
I^2t - value	I^2t	$t_P = 10\text{ ms}$, $V_R = 0\text{ V}$	$T_{vj} = 125\text{ }^{\circ}\text{C}$	150	kA^2s
			$T_{vj} = 175\text{ }^{\circ}\text{C}$	145	

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 1600\text{ A}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ }^\circ\text{C}$	1.70	2.03	V
			$T_{vj} = 125\text{ }^\circ\text{C}$	1.65	1.96	
			$T_{vj} = 175\text{ }^\circ\text{C}$	1.55	1.91	

(table continues...)

Table 6 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Peak reverse recovery current	I_{RM}	$V_{CC} = 600\text{ V}$, $I_F = 1600\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 9350\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	865		A
			$T_{vj} = 125\text{ °C}$	1080		
			$T_{vj} = 175\text{ °C}$	1180		
Recovered charge	Q_r	$V_{CC} = 600\text{ V}$, $I_F = 1600\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 9350\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	160		μC
			$T_{vj} = 125\text{ °C}$	305		
			$T_{vj} = 175\text{ °C}$	400		
Reverse recovery energy	E_{rec}	$V_{CC} = 600\text{ V}$, $I_F = 1600\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 9350\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	75		mJ
			$T_{vj} = 125\text{ °C}$	130		
			$T_{vj} = 175\text{ °C}$	170		
Thermal resistance, junction to case	R_{thJC}	per diode			50.7	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per diode		25.2		K/kW
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	°C

Note: $T_{vj\text{ op}} > 150\text{ °C}$ is only allowed for operation at overload conditions. For detailed specifications please refer to AN2018-14.

4 NTC-Thermistor

Table 7 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	$T_{NTC} = 25\text{ °C}$		5		kΩ
Deviation of R_{100}	$\Delta R/R$	$T_{NTC} = 100\text{ °C}$, $R_{100} = 493\text{ Ω}$	-5		5	%
Power dissipation	P_{25}	$T_{NTC} = 25\text{ °C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15\text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15\text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15\text{ K}))]$		3433		K


Note: For detailed specifications please refer to AN2009-10.

5 Characteristics diagrams

Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{GE} = 15\text{ V}$



Output characteristic field (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$T_{vj} = 175^\circ\text{C}$



Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$


$V_{CE} = 20\text{ V}$



Switching losses (typical), IGBT, Inverter

$E = f(I_C)$


$R_{Goff} = 1\ \Omega$, $R_{Gon} = 0.35\ \Omega$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$



5 Characteristics diagrams


Switching losses (typical), IGBT, Inverter

$E = f(R_G)$
 $I_C = 1600\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$




Transient thermal impedance , IGBT, Inverter

$Z_{th} = f(t)$




Switching times (typical), IGBT, Inverter

$t = f(I_C)$
 $R_{Goff} = 1\ \Omega$, $R_{Gon} = 0.35\ \Omega$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $T_{vj} = 175\text{ °C}$



Reverse bias safe operating area (RBSOA), IGBT, Inverter

$I_C = f(V_{CE})$
 $R_{Goff} = 1\ \Omega$, $V_{GE} = \pm 15\text{ V}$, $T_{vj} = 175\text{ °C}$




5 Characteristics diagrams

Switching times (typical), IGBT, Inverter

$t = f(R_G)$


$I_C = 1600\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $T_{vj} = 175\text{ }^\circ\text{C}$



Capacity characteristic (typical), IGBT, Inverter

$C = f(V_{CE})$


$f = 100\text{ kHz}$, $V_{GE} = 0\text{ V}$, $T_{vj} = 25\text{ }^\circ\text{C}$



Gate charge characteristic (typical), IGBT, Inverter


$V_{GE} = f(Q_G)$

$I_C = 1600\text{ A}$, $T_{vj} = 25\text{ }^\circ\text{C}$



Forward characteristic (typical), Diode, Inverter


$I_F = f(V_F)$



5 Characteristics diagrams


Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$
 $R_{Gon} = R_{Gon}(IGBT) , V_{CC} = 600 V$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$
 $I_F = 1600 A, V_{CC} = 600 V$




Transient thermal impedance, Diode, Inverter

$Z_{th} = f(t)$



Temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



6 Circuit diagram




Figure 1




Figure 2

8 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
			
71549142846550549911530		71549142846550549911530	

Figure 3

Revision history

Document revision	Date of release	Description of changes
V1.0	2020-02-18	Target datasheet
V1.1	2020-08-21	Target datasheet
n/a	2020-09-01	Datasheet migrated to a new system with a new layout and new revision number schema: target or preliminary datasheet = 0.xy; final datasheet = 1.xy
1.10	2020-11-18	
1.11	2022-05-17	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2022-05-17

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2022 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAAY152-004

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.