









P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- THREADED REAR SPACERS / FRONT THREADED LOCKS:
COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- SLEEVES: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 164A12179X CONEC ABC



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance			scale:	2:1 (5:1)											
													dim. in mm	material:	SEE NOTES										
										DO NOT ALTER CAD DRAWING BY HAND										date		name		title: D-SUB FEMALE 9pos. SOLDER PIN STRAIGHT with threaded rear spacer and front threaded lock	
																				drawn		16.03.11	Schmidt		
appd.		16.03.11	Fischer																						
norm																									
										d-old				dwg no: 16K2A2696		DIN-A3 sh: 1									
a		Origin																							
rev.		description		date				name																	
														part no:		164A12179X									

CONEC®

DIN-A3
sh: 1