

COAXIAL CONNECTOR, MMBX, 50 Ohm, Straight PCB jack (female)
82_MMBX-S50-0-3/111_N

Properties

- Smallest board-to-board distance
- Very high frequencies
- Excellent return loss values
- Blind mateable
- Reliable and secure connection



Product configuration		
Interface type	Gender	Standard
MMBX	jack	HUBER+SUHNER-MMBX

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	LCP (Liquid crystal polymer)	

Electrical data	
Impedance	50 Ω
Interface frequency	12.4 GHz

Mechanical data	
Weight	0.0006 kg
Mating cycles	100
Board mounting type	surface mount
Height above PCB HA	3.45 mm
Height of stand off HS	0.6 mm

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force max	30 N	30 N

COAXIAL CONNECTOR, MMBX, 50 Ohm, Straight PCB jack (female)
82_MMBX-S50-0-3/111_N

Environmental data			
Operation temperature		-55 °C ... 155 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23015527			6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
23011273			6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
23031931			6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
23015527	82_MMBX-S50-0-3/111_NE		Single
23011273	82_MMBX-S50-0-3/111_NH		Bulk 100 pcs
23031931	82_MMBX-S50-0-3/111_NM		Tape and Reel
Additional Information			
Remarks		PCB connector with stand-offs	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P38045 / Date of publication: 12.07.2025 / uncontrolled copy