
All orders placed will be shipped out as usual, delivery times are expected to be affected due to COVID-19.Thank you for your continued support. Read More

Register to Get $10 Shipping Coupon



ESP32 WIFI+BLE Module (IPEX antenna)

SKU:DFR0623 Brand:Other Reward Points: 50

Quantity Based

QTY	DISCOUNT
3-4	
5-9	
10+	

* Model: IPEX Antenna PCB Antenna

Quantity: - +

ADD TO CART

Frequently Bought Together

ESP32 WIFI+BLE Module (IPEX antenna) + ESP32 WI... antenna) + Gravity: WiF... Module =

You have choosen:0
Total amount:

BUY IT NOW

INTRODUCTION

ESP32-WROVER-B is a highly-integrated generic WiFi-BT-BLE-MCU module with steady performance and low power consumption. It features an IPEX antenna, a 4MB external SPI flash and 64-Mbit SPI PSRAM that operates at 3.3V. The module targets a wide variety of applications from low power sensor networks to the most demanding tasks, such as voice encoding, music streaming, and MP3 decoding.
This module employs the ESP32-D0WD chip of ESP32 series and also combines 2.4GHz WiFi and dual-mode Bluetooth. There are two CPU cores that can be individually controlled, and the CPU clock frequency is adjustable from 80MHz to 240 MHz. The user may also power off the CPU and make use of the low-power co-processor to constantly monitor the peripherals for changes or crossing thresholds. ESP32 integrates a rich set of peripherals, including capacitive touch sensors, Hall sensors, SD card interface, Ethernet, high-speed SPI, UART, I2C, and I2S.

The integration of Bluetooth, Bluetooth LE and WiFi ensures that a wide range of applications can be covered: using WiFi allows a large physical range and direct connection to the Internet through a WiFi router while using Bluetooth allows the user to conveniently connect to the phone or broadcast low energy beacons for its detection. The sleep current of the ESP32 chip is less than 5 μA, making it suitable for battery-powered and wearable electronics applications. The module supports a data rate of up to 150 Mbps, and 20 dBm output power at the antenna to ensure the widest physical range. As such the module does offer industry-leading specifications and the best performance for electronic integration, range, power consumption, and connectivity.

The operating system chosen for ESP32 is freeRTOS with LwIP; TLS 1.2 with hardware acceleration is built-in as well. Secure (encrypted) over the air (OTA) upgrade is also supported so that users can upgrade their products even after their release.

Downloaded from Arrow.com.



Dimension Diagram

SPECIFICATION

Certification

- RF Certification: FCC/CE-RED/IC/TELEC/KCC/SRRC/NCC
- Bluetooth Certification: BQB
- Green Certification: RoHS/REACH

Test

- Reliability: HTOL/HTSL/uHAST/TCT/ESD

Wi-Fi

- Protocols: 802.11 b/g/n (802.11n up to 150Mbps)
  A-MPDU and A-MSDU aggregation and 0.4μs guard interval support
- Frequency Range: 2.4GHz ~2.5GHz

Bluetooth

- Protocols: Bluetooth v4.2 BR/EDR and BLE specification
- Radio: NZIF receiver with-97 dBm sensitivity
  Class-1, class-2 and class -3 transmitter AFH
- Audio: CVSD and SBC

Hardware

- Module Interface: SD card, UART, SPI, SDIO, I2C, LED PWM, Motor PWM, I2S, IR, pulse counter, GPIO, capacitive touch sensor, ADC, DAC
- On-chip Sensor: Hall sensor
- Integrated Crystal: 40 MHz crystal
- Integrated SPI Flash: 4MB
- Integrated PSRAM: 8MB
- Operating Voltage/Power Supply: 2.7V~3.6V
- Minimum Current Delivered by Power Supply: 500mA
- Recommended Operating Temperature Range: –40°C~65°C
- Package Size: (18.00±0.10)mm×(31.40±0.10)mm×(3.30±0.10)mm

DOCUMENTS

- More Documents


SHIPPING LIST

- ESP32 WIFI+BLE Module (IPEX antenna) x1

REVIEW

Downloaded from Arrow.com.

FAQ



Sign up for exclusive offers!

Your email address →

Like us on

DFROBOT DRIVE THE FUTURE

INFORMATION

About Us
Warranty
Privacy Policy
Shipping
Payment
FAQ

CUSTOMER SERVICE

DFRobot Distributors
Contact us
Site Map

MY ACCOUNT

Affiliates
Specials
Coupon

Downloaded from Arrow.com.