



Search by part # or keyword



Products

Industries & Solutions

Resources

TE Store


Sign In



Connectors > PCB Connectors > Wire-To-Board Connectors > Housings

6-440129-3

HPI 2.0MM,HSG,3POS,BLACK



HPI

TE Internal #: **6-440129-3**
TE Internal Description: **HPI 2.0MM,HSG,3POS,BLACK**

Connector System : **Wire-to-Board**
Number of Positions : **3**
Centerline (Pitch) : **2 mm [.079 in]**
Termination Method to Wire & Cable : **Crimp**
Number of Rows : **1**

[Similar Products](#)

Compatible Parts & Tooling

We are here to help!
Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Feedback

Documents

Features

Product Compliance

Product Drawings

HPI 2.0MM,HSG,3POS,BLACK
 [HPI 2.0MM,HSG,3POS,BLACK](#) English

CAD Files

Customer View Model
 [ENG_CVM_CVM_6-440129-3_C1.3d_igs.zip](#)
English
Customer View Model
 [ENG_CVM_CVM_6-440129-3_C1.3d_stp.zip](#)
English
3D PDF
 [3D_CVM_CVM_6-440129-3_C1.pdf](#) 3D
Customer View Model
 [ENG_CVM_CVM_6-440129-3_C1.2d_dxf.zip](#)
English

Datasheets & Catalog Pages

1-1773713-
2_HIGH_PERFORMANCE_INTERCONNECT_QUICK_REFERENCE_GUIDE_EN
 [ENG_DS_1-1773713-2_HPI_QRG_EN_0114_1-1773713-2HPI_Connectors_0114.pdf](#) English

Product Specifications

Product Specification
 [ENG_SS_108-57100_D.pdf](#) English
Qualification Test Report
 [ENG_SS_108-57058_B.pdf](#) English







Agency Approvals	UL ENG_AAD_UL_E28476_20001207__C.pdf English UL Report ENG_AAD_UL_CERT_ML_E186634_E28476_20001207_A.pdf English CSA Certificate ENG_AAD_CSA_222156_6233_1475575_A.pdf English
	Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.
Product Type Features	Connector System : Wire-to-Board Sealable : No Connector & Contact Terminates To : Wire & Cable Glow Wire Rating : Standard Part - Not Glow Wire Strain Relief : Without Connector Type : Housing Connector Style : Receptacle Product Type : Connector
Configuration Features	Number of Positions : 3 Number of Rows : 1
Electrical Characteristics	Insulation Resistance (MΩ): 1000 Dielectric Withstanding Voltage : 1000 VAC Operating Voltage : 250 VAC
Body Features	Color : Black
Contact Features	Contact Base Material : Copper Alloy Contact Current Rating (Max) (A): 3 Contact Type : Socket Contact Layout : Inline
Termination Features	Termination Method to Wire & Cable : Crimp
Mechanical Attachment	PCB Mount Retention : Without Mating Connector Lock Type : Detent Panel Mount Feature : Without Mating Connector Lock : With Mating Retention : With Mating Retention Type : Detent Connector Mounting Type : Cable Mount (Free-Hanging) Locking Interface : Without Mating Alignment Type : Polarization Mating Alignment : With

Housing Features	Centerline (Pitch) : 2 mm [.079 in] Housing Configuration : Both Ends Closed Housing Material : Thermoplastic Housing Color : Black
Dimensions	Wire Size (mm²): .05 – .22 Wire Size (AWG): 30 – 24 Length : 7.8 mm [.307 in] Insulation Diameter : .9 – 1.5 mm [.0354 – .059 in] Height : 4.5 mm [.177 in] Width : .272 in, 6.9 mm
Usage Conditions	Operating Temperature Range : -25 – 85 °C [-13 – 185 °F]
Operation/Application	Circuit Application : Power & Signal For Use With : 440054-x- 440205-x- 1775470-x- 440055-x- 1734827-x- 1775469-x
Industry Standards	UL Flammability Rating : UL 94V-0
Packaging Features	Packaging Method : Bag/Carton Packaging Quantity : 1000
EU RoHS Directive 2011/65/EU <i>This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).</i>	
EU ELV Directive 2000/53/EC	
China RoHS 2 Directive MIIT Order No 32, 2016	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	
Solder Process Capability	Not applicable for solder process capability

Compliance	
Compliance Documents	There may be Environmental Compliance related documents on the DOCUMENTATION Tab
Disclaimer	<p>This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach</p>

Products with Similar Specs

View All Similar Products

THIS PRODUCT	TOP RESULTS ?		
<div>WIRE-TO-BOARD CONNECTOR...</div> <div>6-440129-3</div> <div>HPI 2.0MM, HSG, 3POS, BLACK</div> <div></div> <div>In-Stock</div> <div>Connector System : Wire-to-Board</div> <div>Number of Positions : 3</div> <div>Centerline (Pitch) : 2 mm</div> <div>Termination Method to Wire & Cable : Crimp</div> <div>Number of Rows : 1</div>	<div>WIRE-TO-BOARD CONNECTOR...</div> <div>4-440129-3</div> <div>HPI 2.0MM, HSG, 3POS, YELLOW</div> <div></div> <div>Non-Stocked</div> <div>Connector System : Wire-to-Board</div> <div>Number of Positions : 3</div> <div>Centerline (Pitch) : 2 mm</div> <div>Termination Method to Wire & Cable : Crimp</div> <div>Number of Rows : 1</div>	<div>WIRE-TO-BOARD CONNECTOR...</div> <div>440129-3</div> <div>2.0MM, HSG, 3POS</div> <div></div> <div>FromIn-Stock</div> <div>Connector System : Wire-to-Board</div> <div>Number of Positions : 3</div> <div>Centerline (Pitch) : 2 mm</div> <div>Termination Method to Wire & Cable : Crimp</div> <div>Number of Rows : 1</div>	<div>WIRE-TO-BOARD CONNECTOR...</div> <div>8-440129-3</div> <div>HPI 2.0MM, HSG, 3POS, RED</div> <div></div> <div>Non-Stocked</div> <div>Connector System : Wire-to-Board</div> <div>Number of Positions : 3</div> <div>Centerline (Pitch) : 2 mm</div> <div>Termination Method to Wire & Cable : Crimp</div> <div>Number of Rows : 1</div>



Wire-to-Board
Connector Contacts
(2)



Wire-to-Board
Connector Housings
(93)



Wire-to-Board
Headers &
Receptacles (136)

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)