

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECO-17-007607	29MAY2017	RK	AS


SPECIFICATIONS:
SINGLE POLE DOUBLE THROW

ELECTRICAL:
CONTACT RATING, 24VAC AT 0.5 AMP (POWER FACTOR 0.4) AND
INRUSH CURRENT OF 2.5 AMP (POWER FACTOR 0.4)
CONTACT RESISTANCE, 30 MILLIOHMS MAX
INSULATION RESISTANCE, 500 MEGOHM MIN
DIELECTRIC STRENGTH, 500 V RMS@ SEA LEVEL
LIFE EXPECTANCY, 2,000 CYCLES

ENVIRONMENTAL:
OPERATING TEMPERATURE, -20 TO +85° C
STORAGE TEMPERATURE, -20 TO +85° C
RESISTANCE TO SOLDER HEAT, PER 109-201, CONDITION A
OMIT SECTION 3.3
TIME OVER LIQUIDUS (217°C) 20 SECONDS MAX
PEAK TEMPERATURE 225°±5°C


1. ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).

- ⚠ NOTE DELETED.
⚠ RESISTANCE TO SOLDER HEAT, PER 109-201 CONDITION B.




NON SHORTING
SCHEMATIC

AR	NONE	GREASE	ACTUATOR LUBRICATION	10
—	NONE	GREASE	CONTACT LUBRICATION	9
1	PASSIVATE	STAINLESS STEEL	SPRING PLATE	8
1	NONE	MUSIC WIRE	COIL SPRING	7
1	AG OVER NICKEL	COPPER TI	MOVING CONTACT	6
6	AG OVER NICKEL	COPPER	FIXED CONTACT/TERMINAL	5
1	NICKEL	COLD ROLLED STEEL	FRAME	4
1	BLACK	LCP UL94 V-0 30% GF	BOARD	3A
—	BLACK	PA66 UL 94HB, 15% GF	BOARD	3
1	BLACK	LCP UL94 V-0 30% GF	ACTUATOR II	2A
—	BLACK	PA66 UL 94HB, 15% GF	ACTUATOR II	2
1	BLACK	LCP UL94 V-0 30% GF	ACTUATOR	1A
—	BLACK	PA66 UL 94HB, 15% GF	ACTUATOR	1
-4	FINISH	MATERIAL	PART DESCRIPTION	ITEM NO.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER	04SEP2007	TE Connectivity	
DIMENSIONS: mm		CHK M.SARVER	—		
		APVD —	—		
		PRODUCT SPEC	—		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	—	SLIDE SWITCH , SPDT, SMT	
0 PLC ± — 1 PLC ± — 2 PLC ± 0.20 3 PLC ± 0.05 4 PLC ± — ANGLES ± 3° FINISH		—	—		
MATERIAL —		WEIGHT 0	A2	00779	C=1977143
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 2	REV J



NOTES

- TAPE, REEL, AND TAPING SHALL MEET THE REQUIREMENTS OF EIA-481-2.
- EMBOSSED TAPE SHALL BE CONDUCTIVE TYPE.
- FOR PART ORIENTATION IN TAPE SEE DETAIL A.
- REEL SHALL CONTAIN 200 PIECES SWITCH
- REEL IDENTIFICATION LABEL SHALL BE PRINTED WITH REEL:
TYCO ELECTRONICS
P/N:1977143-3 & -4
QTY:200PCS
DATE CODE:XXXX

SEE DETAIL A
4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER	04SEP2007	 TE Connectivity			
DIMENSIONS: mm		CHK M.SARVER	—				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME — SLIDE SWITCH , SPDT, SMT			
	0 PLC ± —		PRODUCT SPEC —				
	1 PLC ± —		—				
	2 PLC ± 0.20		—				
	3 PLC ± 0.05		APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C=1977143	RESTRICTED TO —
	4 PLC ± —		—				
	ANGLES ± 3°		—				
	MATERIAL —		WEIGHT —				
		CUSTOMER DRAWING		SCALE 4:1	SHEET 2 of 2	REV J	