

Part Number : 1300120587
Product Description : Mini-Change C-Size Double-Ended Cordset, 12 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 2.0m (6.56') Length
Series Number : 130012
Status : Obsolete
Product Category : Industrial Cable Assemblies
Engineering Part Number : 332030K04M020

Documents and Resources

Drawings

1300120587_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Obsolete

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Industrial Cable Assemblies
Series	130012
Description	Mini-Change C-Size Double-Ended Cordset, 12 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	FF
Type	Double Ended
UPC	78172532725

Agency

UL	E152210

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	600V

Physical

Cable Diameter	14.99mm (.590")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE

Obsolete

Downloaded from Arrow.com.

Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Anodized Aluminum, Electrophoretic Zinc Alloy
Material - Plating Mating	Gold
Net Weight	255.000/g
Orientation	Straight to Straight
Poles	12
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	16

This document was generated on Sep 09, 2026

Obsolete

Downloaded from Arrow.com.