

200mW, NPN Small Signal Transistor

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
V_{CBO}	30-80	V
V_{CEO}	30-65	V
V_{EBO}	5-6	V
I_C	0.1	A
h_{FE}	220-800	




APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- Lighting application
- On-board DC/DC converter



MECHANICAL DATA

- Case: SOT-23
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- Weight: 8mg (approximately)

PACKAGE: SOT-23	PIN CONFIGURATION	CIRCUIT DIAGRAM
		

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER		SYMBOL	VALUE	UNIT
Power dissipation		P_D	200	mW
Collector-base voltage, emitter open	BC846	V_{CBO}	80	V
	BC847		50	
	BC848		30	
Collector-emitter voltage, base open	BC846	V_{CEO}	65	V
	BC847		45	
	BC848		30	
Emitter-base voltage, collector open	BC846	V_{EBO}	6	V
	BC847		6	

	BC848		5	
Collector current, dc		I_C	0.1	A
Junction temperature		T_J	-55 to +150	°C
Storage temperature		T_{STG}	-55 to +150	°C

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	CONDITIONS		SYMBOL	MIN	MAX	UNIT
Collector cutoff current	$V_{CB} = 30\text{ V}, I_E = 0$		I_{CBO}	-	100	nA
Emitter cutoff current	$V_{EB} = 5\text{ V}, I_C = 0$		I_{EBO}	-	0.1	μA
Collector-base voltage	$I_C = 10\text{ }\mu\text{A}, I_E = 0$	BC846	V_{CBO}	80	-	V
		BC847		50	-	
		BC848		30	-	
Collector-emitter voltage	$I_C = 10\text{ mA}, I_B = 0$	BC846	V_{CEO}	65	-	V
		BC847		45	-	
		BC848		30	-	
Emitter-base voltage	$I_E = 1\text{ }\mu\text{A}, I_C = 0$	BC846	V_{EBO}	6	-	V
		BC847		6	-	
		BC848		5	-	
DC current gain	$V_{CE} = 5\text{ V}, I_C = 2\text{ mA}$	BC846A/BC847A/BC848A	h_{FE}	110	220	
		BC846B/BC847B/BC848B		200	450	
		BC847C/BC848C		420	800	
Collector-emitter saturation voltage	$I_C = 100\text{ mA}, I_B = 5\text{ mA}$		$V_{CE(sat)}$	-	0.5	V
Base-emitter saturation voltage	$I_C = 100\text{ mA}, I_B = 5\text{ mA}$		$V_{BE(sat)}$	-	1.1	V
Transition frequency	$V_{CE} = 5\text{ V}, I_C = 10\text{ mA}, f = 100\text{ MHz}$		f_T	100	-	MHz

ORDERING INFORMATION

ORDERING CODE	PACKAGE	PACKING	DEVICE MARKING
BC846A RFG	SOT-23	3K / 7" Reel	1A
BC846B RFG	SOT-23	3K / 7" Reel	1B
BC847A RFG	SOT-23	3K / 7" Reel	1E
BC847B RFG	SOT-23	3K / 7" Reel	1F
BC847C RFG	SOT-23	3K / 7" Reel	1G
BC848A RFG	SOT-23	3K / 7" Reel	1J

BC848B RFG	SOT-23	3K / 7" Reel	1K
BC848C RFG	SOT-23	3K / 7" Reel	1L
BC846A R5G	SOT-23	10K / 13" Reel	1A
BC846B R5G	SOT-23	10K / 13" Reel	1B
BC847A R5G	SOT-23	10K / 13" Reel	1E
BC847B R5G	SOT-23	10K / 13" Reel	1F
BC847C R5G	SOT-23	10K / 13" Reel	1G
BC848A R5G	SOT-23	10K / 13" Reel	1J
BC848B R5G	SOT-23	10K / 13" Reel	1K
BC848C R5G	SOT-23	10K / 13" Reel	1L

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Static Characteristic




Fig. 2 DC Current Gain




Fig.3 Base-Emitter Saturation Voltage
Collector-Emitter Saturation Voltage





Fig.4 Base-Emitter On Voltage



CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.5 Collector Output Capacitance











Fig. 6 Current Gain Bandwidth Product



PACKAGE OUTLINE DIMENSIONS

SOT-23



NOTES: UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
3. PACKAGE OUTLINE REFERENCE: JEDEC TO-236, ISSUE H, VARIATION AA.

4. MOLDED PLASTIC BODY DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.

5. DWG NO. REF: HQ2SD07-SOT23JEDEC-104 REV B.

P/N = Device marking

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.